



Pulley flanges

Dimensions of flanges used with pulleys



Aluminium



Steel

Part number	ØA	ØD	E	Material	Also used
10T2,5X	6,00	13,00	1,00	Aluminium	-
13T2,5X	6,00	16,00	1,00	Aluminium	-
16T2,5X	8,00	18,00	1,00	Aluminium	-
19T2,5X	8,00	20,00	1,00	Aluminium	-
31T2,5X	10,00	18,00	1,00	Aluminium	-
32T2,5X	12,00	20,00	1,00	Aluminium	-
10T2,5Y	6,00	13,00	8,50	Aluminium	-
13T2,5Y	6,00	16,00	8,50	Aluminium	-
16T2,5Y	8,00	18,00	8,50	Aluminium	-
19T2,5Y	8,00	20,00	8,50	Aluminium	-
31T2,5Y	10,00	18,00	8,50	Aluminium	-
32T2,5Y	12,00	20,00	8,50	Aluminium	-
12WX	6,00	11,00	0,80	Aluminium	-
15WX	8,00	13,00	0,80	Aluminium	-
20WX	10,00	17,00	0,80	Aluminium	-
22WX	12,00	20,00	0,80	Aluminium	-
26WX	13,00	21,00	0,80	Aluminium	-
30WX	16,00	24,00	0,80	Aluminium	-
40WX	19,05	28,00	0,80	Aluminium	-
42WX	22,00	32,00	0,80	Aluminium	-
46WX	24,00	32,00	0,80	Aluminium	-
48WX	26,00	34,00	0,80	Aluminium	-
12WY	6,00	11,00	6,00	Aluminium	-
15WY	8,00	13,00	6,00	Aluminium	-
20WY	10,00	17,00	6,00	Aluminium	-
22WY	12,00	20,00	6,00	Aluminium	-
26WY	13,00	21,00	6,00	Aluminium	-
30WY	16,00	24,00	6,00	Aluminium	-
40WY	19,05	28,00	6,00	Aluminium	-
42WY	22,00	32,00	6,00	Aluminium	-
46WY	24,00	32,00	6,00	Aluminium	-
48WY	26,00	34,00	6,00	Aluminium	-

Part number	ØA	ØD	E	Material	Also used
11XL	12,70	23,62	1,22	Aluminium	-
12XL	14,27	25,15	1,22	Aluminium	-
14XL	17,44	28,44	1,22	Aluminium	-
15XL	19,05	29,97	1,22	Aluminium	-
16XL	20,63	31,74	1,22	Aluminium	-
18XL	22,22	34,80	1,22	Aluminium	-
20XL	25,40	38,10	1,22	Aluminium	-
21XL	26,97	39,68	1,22	Aluminium	-
22XL	28,57	41,28	1,22	Aluminium	-
24XL	31,75	44,70	1,22	Aluminium	-
26XL	36,50	49,25	1,22	Aluminium	-
28XL	38,10	51,05	1,22	Aluminium	-
30XL	41,40	54,36	1,22	Aluminium	-
10L	22,23	34,93	1,63	Aluminium	-
12L	28,57	41,28	1,63	Aluminium	-
14L	33,33	49,20	1,63	Aluminium	-
15L	37,10	52,39	1,63	Aluminium	-
16L	41,27	55,56	1,63	Aluminium	-
17L	42,86	57,15	1,63	Aluminium	-
14H	44,45	61,91	1,63	Aluminium	18L
15H	47,62	66,68	1,63	Aluminium	19L / 20L
16H	50,80	69,85	1,63	Aluminium	21L
17H	55,56	74,61	1,63	Aluminium	22L
18H	60,32	79,38	1,63	Aluminium	23L / 24L
19H	63,50	82,55	1,63	Steel	25L
20H	66,67	85,73	1,63	Steel	26L
21H	71,43	90,49	1,63	Steel	27L / 38L
22H	76,20	95,25	1,63	Steel	29L
23H	79,37	98,43	1,63	Steel	30L
24H	82,55	103,19	1,63	Steel	32L
25H	85,72	106,36	1,63	Steel	33L
26H	88,91	111,13	1,63	Steel	34L
27H	92,07	114,30	1,63	Steel	36L
28H	96,83	119,06	1,63	Steel	37L
30H	104,77	127,00	1,63	Steel	40L
31H	111,12	131,76	1,63	Steel	-
32H	112,71	134,94	1,63	Steel	42L / 43L
33H	120,65	139,70	1,63	Steel	44L
34H	120,65	142,88	1,63	Steel	45L
36H	127,00	150,81	1,63	Steel	48L
38H	136,52	158,75	1,63	Steel	-
40H	146,05	168,28	1,63	Steel	53L
42H	152,40	176,21	1,63	Steel	-
44H	158,75	184,15	1,63	Steel	58L / 59L
46H	168,28	187,33	1,63	Steel	60L
48H	174,62	200,02	1,63	Steel	64L