Quadro linear ball bearing unit

Alu


BPQ

Included 4 linear ball bearings

NUOVO !



- **Block bearings allowing the creation of a linear table with 2 guide shafts**
- Supplid with 4 compact linear ball bearings
- Protected with wiper seals
- Working T°: from +5°C to +80°C
- Max speed: 2m/s
- Materials:
  Housing: anodised aluminium
  Ball bearing: plastic housing, NBR wipers



Part number	F* (daN)	C* (Nm)	M* (Nm)
BPQ12-4	17 / 10	8 / 5	16 / 10
BPQ16-4	34 / 20	17 / 11	32 / 19
BPQ20-4	64 / 40	29 / 18	55 / 34
BPQ25-4	125 / 80	52 / 30	90 / 60

*load: max values, static / dynamic

DISCOUNTS

Qty	1+	2+	4+
Disc.	List	-5%	On request

Part number	For shaft ØA	B	ØD1	ØD2	ØD3	ØD4	E	H	N	P2	U	Weight (kg)	Price each
BPQ12-4	Ø12	85	M6	10,2	M4	19	73	32	2	7	46	0,53	174,82 €
BPQ16-4	Ø16	98	M6	10,2	M5	31	88	36	2	7	56	0,75	189,38 €
BPQ20-4	Ø20	130	M8	13,5	M5	31	115	46	2	8	72	1,75	241,23 €
BPQ25-4	Ø25	160	M10	17,0	M6	45	140	56	4	11	88	3,20	320,82 €

Dimensions in mm