Cylindrical drill bushing

New Stock

CDP

Treated steel

- ***For guiding drill bits during repetitive drilling or countersinking operations***
- *Good resistance in operation*
- *Material:*
  Case hardened steel



Info.

- *Bore tolerance: DH7*

Advantages

- *Facilitates the drilling operation and avoids wear of the drill bit*
- *Ensures high repeatability*

IN STOCK*
Otherwise contact us


DISCOUNTS

Qty	1+	5+	10+	20+
Disc.	List	-5%	-10%	On request

Part number	Ød1	l1	Ød2 (n6)	r	Weight (g)	Price each 1 to 4
CDP2-5-6	2	6	5	1	0,7	4,98 €
CDP2-5-9	2	9	5	1	1,1	5,43 €
CDP2.1-5-6	2,1	6	5	1	0,7	5,00 €
CDP2.1-5-9	2,1	9	5	1	1,1	5,45 €
CDP2.5-5-6	2,5	6	5	1	0,7	5,00 €
CDP2.5-5-9	2,5	9	5	1	1	5,45 €
CDP3-6-8	3	8	6	1	1,3	4,98 €
CDP3-6-12	3	12	6	1	1,9	5,43 €
CDP3-6-16	3	16	6	1	2,6	11,09 €
CDP3.1-6-8	3,1	8	6	1	1,2	4,98 €
CDP3.1-6-12	3,1	12	6	1	1,9	5,43 €
CDP3.1-6-16	3,1	16	6	1	2,5	11,09 €
CDP3.5-7-8	3,5	8	7	1	1,7	7,82 €
CDP3.5-7-12	3,5	12	7	1	2,6	5,15 €
CDP3.5-7-16	3,5	16	7	1	3,6	11,09 €
CDP4-7-8	4	8	7	1	1,5	4,50 €
CDP4-7-12	4	12	7	1	2,4	5,15 €
CDP4-7-16	4	16	7	1	3,2	11,09 €
CDP4.1-8-8	4,1	8	8	1	2,2	4,68 €
CDP4.1-8-12	4,1	12	8	1	3,4	5,43 €
CDP4.1-8-16	4,1	16	8	1	4,6	9,73 €
CDP4.5-8-8	4,5	8	8	1	2,1	4,68 €
CDP4.5-8-12	4,5	12	8	1	3,1	5,43 €
CDP4.5-8-16	4,5	16	8	1	4,2	9,73 €
CDP5-8-8	5	8	8	1	1,8	4,68 €
CDP5-8-12	5	12	8	1	2,8	5,43 €
CDP5-8-16	5	16	8	1	3,7	9,73 €
CDP5.1-10-10	5,1	10	10	1,5	4,4	5,15 €
CDP5.1-10-16	5,1	16	10	1,5	7,1	5,93 €

Part number	Ød1	l1	Ød2 (n6)	r	Weight (g)	Price each 1 to 4
CDP5.1-10-20	5,1	20	10	1,5	8,9	10,64 €
CDP5.5-10-10	5,5	10	10	1,5	4,1	5,15 €
CDP5.5-10-16	5,5	16	10	1,5	6,7	5,93 €
CDP5.5-10-20	5,5	20	10	1,5	8,4	10,64 €
CDP6-10-10	6	10	10	1,5	3,8	5,15 €
CDP6-10-16	6	16	10	1,5	6,1	5,93 €
CDP6-10-20	6	20	10	1,5	7,7	10,64 €
CDP6.1-12-10	6,1	10	12	1,5	6,3	5,43 €
CDP6.1-12-16	6,1	16	12	1,5	10	6,12 €
CDP6.1-12-20	6,1	20	12	1,5	13	11,09 €
CDP6.5-12-10	6,5	10	12	1,5	6	5,43 €
CDP6.5-12-16	6,5	16	12	1,5	9,7	6,12 €
CDP6.5-12-20	6,5	20	12	1,5	12	11,09 €
CDP7-12-10	7	10	12	1,5	5,6	5,43 €
CDP7-12-16	7	16	12	1,5	9,1	6,12 €
CDP7-12-20	7	20	12	1,5	11	11,09 €
CDP7.1-12-10	7,1	10	12	1,5	5,5	5,43 €
CDP7.1-12-16	7,1	16	12	1,5	9	6,12 €
CDP7.1-12-20	7,1	20	12	1,5	11	11,09 €
CDP7.5-12-10	7,5	10	12	1,5	5,1	5,43 €
CDP7.5-12-16	7,5	16	12	1,5	8,4	6,12 €
CDP7.5-12-20	7,5	20	12	1,5	11	11,09 €
CDP8-12-10	8	10	12	1,5	4,7	5,43 €
CDP8-12-16	8	16	12	1,5	7,6	6,12 €
CDP8-12-20	8	20	12	1,5	9,6	11,09 €
CDP8.1-15-12	8,1	12	15	2	11	5,65 €
CDP8.1-15-20	8,1	20	15	2	19	6,91 €
CDP8.1-15-25	8,1	25	15	2	24	11,98 €
CDP8.5-15-12	8,5	12	15	2	11	5,65 €

**Depending on availability - Dimensions in mm*



IN STOCK*
Otherwise contact us

DISCOUNTS

Qty	1+	5+	10+	20+
Disc.	List	-5%	-10%	On request

Part number	Ød1	l1	Ød2 (n6)	r	Weight (g)	Price each 1 to 4
CDP8.5-15-20	8,5	20	15	2	18	6,91 €
CDP8.5-15-25	8,5	25	15	2	23	11,98 €
CDP9-15-12	9	12	15	2	10	5,65 €
CDP9-15-20	9	20	15	2	17	6,91 €
CDP9-15-25	9	25	15	2	22	11,98 €
CDP9.1-15-12	9,1	12	15	2	10	5,65 €
CDP9.1-15-20	9,1	20	15	2	17	6,91 €
CDP9.1-15-25	9,1	25	15	2	21	11,98 €
CDP9.5-15-12	9,5	12	15	2	9,5	5,65 €
CDP9.5-15-20	9,5	20	15	2	16	6,91 €
CDP9.5-15-25	9,5	25	15	2	20	11,98 €
CDP10-15-12	10	12	15	2	8,8	5,68 €
CDP10-15-20	10	20	15	2	15	6,93 €
CDP10-15-25	10	25	15	2	19	12,03 €
CDP10.1-18-12	10,1	12	18	2	16	6,60 €
CDP10.1-18-20	10,1	20	18	2	27	8,03 €
CDP10.1-18-25	10,1	25	18	2	33	12,44 €
CDP10.5-18-12	10,5	12	18	2	15	6,60 €
CDP10.5-18-20	10,5	20	18	2	26	8,03 €
CDP10.5-18-25	10,5	25	18	2	32	12,44 €
CDP11-18-12	11	12	18	2	14	6,60 €
CDP11-18-20	11	20	18	2	24	8,03 €
CDP11-18-25	11	25	18	2	31	12,44 €
CDP11.1-18-12	11,1	12	18	2	14	6,60 €
CDP11.1-18-20	11,1	20	18	2	24	8,03 €
CDP11.1-18-25	11,1	25	18	2	30	12,44 €
CDP11.5-18-12	11,5	12	18	2	14	6,60 €
CDP11.5-18-20	11,5	20	18	2	23	8,03 €
CDP11.5-18-25	11,5	25	18	2	29	12,44 €
CDP12-18-12	12	12	18	2	13	6,60 €
CDP12-18-20	12	20	18	2	22	8,03 €
CDP12-18-25	12	25	18	2	27	12,44 €
CDP12.1-22-16	12,1	16	22	2	32	7,35 €
CDP12.1-22-28	12,1	28	22	2	57	9,96 €
CDP12.1-22-36	12,1	36	22	2	74	15,63 €
CDP12.5-22-16	12,5	16	22	2	31	7,35 €
CDP12.5-22-28	12,5	28	22	2	66	9,96 €
CDP12.5-22-36	12,5	36	22	2	69	15,63 €
CDP13-22-16	13	16	22	2	30	7,35 €
CDP13-22-28	13	28	22	2	53	9,96 €

Part number	Ød1	l1	Ød2 (n6)	r	Weight (g)	Price each 1 to 4
CDP13-22-36	13	36	22	2	69	15,63 €
CDP14-22-16	14	16	22	2	27	7,35 €
CDP14-22-28	14	28	22	2	49	9,96 €
CDP14-22-36	14	36	22	2	63	15,63 €
CDP15-22-16	15	16	22	2	25	7,35 €
CDP15-22-28	15	28	22	2	44	9,96 €
CDP15-22-36	15	36	22	2	56	15,63 €
CDP16-26-16	16	16	26	2	45	9,96 €
CDP16-26-28	16	28	26	2	71	12,57 €
CDP16-26-36	16	36	26	2	92	19,56 €
CDP16.1-26-16	16,1	16	26	2	40	15,14 €
CDP16.1-26-28	16,1	28	26	2	71	18,51 €
CDP16.1-26-36	16,1	36	26	2	91	26,26 €
CDP16.5-26-16	16,5	16	26	2	39	9,96 €
CDP16.5-26-28	16,5	28	26	2	68	12,57 €
CDP16.5-26-36	16,5	36	26	2	88	19,56 €
CDP17-26-16	17	16	26	2	37	9,96 €
CDP17-26-28	17	28	26	2	65	12,57 €
CDP17-26-36	17	36	26	2	84	19,56 €
CDP18-26-16	18	16	26	2	33	9,96 €
CDP18-26-28	18	28	26	2	59	12,57 €
CDP18-26-36	18	36	26	2	77	19,56 €
CDP19-30-20	19	20	30	3	64	12,29 €
CDP19-30-36	19	36	30	3	117	15,42 €
CDP19-30-45	19	45	30	3	147	24,91 €
CDP20-30-20	20	20	30	3	59	12,29 €
CDP20-30-36	20	36	30	3	108	15,42 €
CDP20-30-45	20	45	30	3	136	24,91 €
CDP20.1-30-20	20,1	20	30	3	59	17,98 €
CDP20.1-30-36	20,1	36	30	3	108	21,76 €
CDP20.1-30-45	20,1	45	30	3	135	33,85 €
CDP22-30-20	22	20	30	3	49	12,29 €
CDP22-30-36	22	36	30	3	90	15,42 €
CDP22-30-45	22	45	30	3	113	24,91 €
CDP25-35-20	25	20	35	3	71	14,53 €
CDP25-35-36	25	36	35	3	130	17,98 €
CDP25-35-45	25	45	35	3	163	28,93 €
CDP30-42-25	30	25	42	3	129	25,97 €
CDP30-42-45	30	45	42	3	235	32,10 €
CDP30-42-56	30	56	42	3	293	48,81 €

*Depending on availability - Dimensions in mm

Flanged drill bushing

Stock

CDPC

Treated steel

- **For guiding drill bits during repetitive drilling or countersinking operations**
- Good resistance in operation
- Material:
  Case hardened steel



Info.

- Bore tolerance: DH7

Advantages

- Facilitates the drilling operation and avoids wear of the drill bit
- Ensures high repeatability

IN STOCK*
Otherwise contact us


DISCOUNTS


Qty	1+	5+	10+	20+
Disc.	List	-5%	-10%	On request

Part number	Ød1	l1	Ød2 (n6)	Ød3	l2	Weight (g)	Price each 1 to 4
CDPC2-5-6	2	6	5	8	2	1,2	6,63 €
CDPC2-5-9	2	9	5	8	2	1,6	7,14 €
CDPC2.1-5-6	2,1	6	5	8	2	1,2	6,63 €
CDPC2.1-5-9	2,1	9	5	8	2	1,5	7,14 €
CDPC2.5-5-6	2,5	6	5	8	2	1,1	6,63 €
CDPC2.5-5-9	2,5	9	5	8	2	1,4	7,14 €
CDPC3-6-8	3	8	6	9	2,5	1,9	6,53 €
CDPC3-6-12	3	12	6	9	2,5	2,6	7,14 €
CDPC3-6-16	3	16	6	9	2,5	3,2	12,48 €
CDPC3.1-6-8	3,1	8	6	9	2,5	1,9	6,53 €
CDPC3.1-6-12	3,1	12	6	9	2,5	2,5	7,14 €
CDPC3.1-6-16	3,1	16	6	9	2,5	3,2	12,48 €
CDPC3.5-7-8	3,5	8	7	10	2,5	2,4	6,17 €
CDPC3.5-7-12	3,5	12	7	10	2,5	3,4	6,96 €
CDPC3.5-7-16	3,5	16	7	10	2,5	4,3	12,48 €
CDPC4-7-8	4	8	7	10	2,5	2,3	6,17 €
CDPC4-7-12	4	12	7	10	2,5	3,1	6,96 €
CDPC4-7-16	4	16	7	10	2,5	3,9	12,48 €
CDPC4.1-8-8	4,1	8	8	11	2,5	3	5,97 €
CDPC4.1-8-12	4,1	12	8	11	2,5	4,2	6,35 €
CDPC4.1-8-16	4,1	16	8	11	2,5	5,3	10,71 €
CDPC4.5-8-8	4,5	8	8	11	2,5	2,9	5,97 €
CDPC4.5-8-12	4,5	12	8	11	2,5	3,9	6,35 €
CDPC4.5-8-16	4,5	16	8	11	2,5	5	10,71 €
CDPC5-8-8	5	8	8	11	2,5	2,6	5,97 €
CDPC5-8-12	5	12	8	11	2,5	3,6	6,35 €
CDPC5-8-16	5	16	8	11	2,5	4,5	10,71 €
CDPC5.1-10-10	5,1	10	10	13	3	5,5	6,17 €
CDPC5.1-10-16	5,1	16	10	13	3	8,2	6,96 €

Part number	Ød1	l1	Ød2 (n6)	Ød3	l2	Weight (g)	Price each 1 to 4
CDPC5.1-10-20	5,1	20	10	13	3	10	11,60 €
CDPC5.5-10-10	5,5	10	10	13	3	5,3	6,17 €
CDPC5.5-10-16	5,5	16	10	13	3	7,9	6,96 €
CDPC5.5-10-20	5,5	20	10	13	3	9,6	11,60 €
CDPC6-10-10	6	10	10	13	3	4,9	6,17 €
CDPC6-10-16	6	16	10	13	3	7,3	6,96 €
CDPC6-10-20	6	20	10	13	3	8,8	11,60 €
CDPC6.1-12-10	6,1	10	12	15	3	7,7	6,96 €
CDPC6.1-12-16	6,1	16	12	15	3	12	7,60 €
CDPC6.1-12-20	6,1	20	12	15	3	14	12,34 €
CDPC6.5-12-10	6,5	10	12	15	3	7,4	6,96 €
CDPC6.5-12-16	6,5	16	12	15	3	11	7,60 €
CDPC6.5-12-20	6,5	20	12	15	3	14	12,34 €
CDPC7-12-10	7	10	12	15	3	7	6,96 €
CDPC7-12-16	7	16	12	15	3	10	7,60 €
CDPC7-12-20	7	20	12	15	3	13	12,34 €
CDPC7.1-12-10	7,1	10	12	15	3	6,9	6,96 €
CDPC7.1-12-16	7,1	16	12	15	3	10	7,60 €
CDPC7.1-12-20	7,1	20	12	15	3	13	12,34 €
CDPC7.5-12-10	7,5	10	12	15	3	6,5	6,96 €
CDPC7.5-12-16	7,5	16	12	15	3	9,7	7,60 €
CDPC7.5-12-20	7,5	20	12	15	3	12	12,34 €
CDPC8-12-10	8	10	12	15	3	6	6,96 €
CDPC8-12-16	8	16	12	15	3	9	7,60 €
CDPC8-12-20	8	20	12	15	3	11	12,34 €
CDPC8.1-15-12	8,1	12	15	18	3	13	7,88 €
CDPC8.1-15-20	8,1	20	15	18	3	25	8,53 €
CDPC8.1-15-25	8,1	25	15	18	3	26	13,38 €
CDPC8.5-15-12	8,5	12	15	18	3	13	7,88 €

*Depending on availability - Dimensions in mm





IN STOCK*
Otherwise contact us

DISCOUNTS

Qty	1+	5+	10+	20+
Disc.	List	-5%	-10%	On request

Part number	Ød1	l1	Ød2 (n6)	Ød3	l2	Weight (g)	Price each 1 to 4
CDPC8.5-15-20	8,5	20	15	18	3	20	8,53 €
CDPC8.5-15-25	8,5	25	15	18	3	25	13,38 €
CDPC9-15-12	9	12	15	18	3	12	7,88 €
CDPC9-15-20	9	20	15	18	3	19	8,53 €
CDPC9-15-25	9	25	15	18	3	23	13,28 €
CDPC9.1-15-12	9,1	12	15	18	3	12	7,88 €
CDPC9.1-15-20	9,1	20	15	18	3	19	8,53 €
CDPC9.1-15-25	9,1	25	15	18	3	23	13,38 €
CDPC9.5-15-12	9,5	12	15	18	3	11	7,88 €
CDPC9.5-15-20	9,5	20	15	18	3	18	8,53 €
CDPC9.5-15-25	9,5	25	15	18	3	22	13,38 €
CDPC10-15-12	10	12	15	18	3	11	7,82 €
CDPC10-15-20	10	20	15	18	3	17	8,47 €
CDPC10-15-25	10	25	15	18	3	20	13,28 €
CDPC10.1-18-12	10,1	12	18	22	4	20	8,47 €
CDPC10.1-18-20	10,1	20	18	22	4	30	9,23 €
CDPC10.1-18-25	10,1	25	18	22	4	37	14,18 €
CDPC10.5-18-12	10,5	12	18	22	4	19	8,47 €
CDPC10.5-18-20	10,5	20	18	22	4	29	9,23 €
CDPC10.5-18-25	10,5	25	18	22	4	36	14,18 €
CDPC11-18-12	11	12	18	22	4	18	8,47 €
CDPC11-18-20	11	20	18	22	4	28	9,23 €
CDPC11-18-25	11	25	18	22	4	34	14,18 €
CDPC11.1-18-12	11,1	12	18	22	4	18	8,47 €
CDPC11.1-18-20	11,1	20	18	22	4	28	9,23 €
CDPC11.1-18-25	11,1	25	18	22	4	34	14,18 €
CDPC11.5-18-12	11,5	12	18	22	4	17	8,47 €
CDPC11.5-18-20	11,5	20	18	22	4	26	9,23 €
CDPC11.5-18-25	11,5	25	18	22	4	33	14,18 €
CDPC12-18-12	12	12	18	22	4	16	8,47 €
CDPC12-18-20	12	20	18	22	4	25	9,23 €
CDPC12-18-25	12	25	18	22	4	31	14,18 €
CDPC12.1-22-16	12,1	16	22	26	4	37	9,70 €
CDPC12.1-22-28	12,1	28	22	26	4	62	13,78 €
CDPC12.1-22-36	12,1	36	22	26	4	78	20,00 €
CDPC12.5-22-16	12,5	16	22	26	4	36	9,70 €
CDPC12.5-22-28	12,5	28	22	26	4	60	13,78 €
CDPC12.5-22-36	12,5	36	22	26	4	76	20,00 €
CDPC13-22-16	13	16	22	26	4	34	9,70 €
CDPC13-22-28	13	28	22	26	4	58	13,78 €

Part number	Ød1	l1	Ød2 (n6)	Ød3	l2	Weight (g)	Price each 1 to 4
CDPC13-22-36	13	36	22	26	4	73	20,00 €
CDPC14-22-16	14	16	22	26	4	32	9,70 €
CDPC14-22-28	14	28	22	26	4	53	13,78 €
CDPC14-22-36	14	36	22	26	4	67	20,00 €
CDPC15-22-16	15	16	22	26	4	29	9,70 €
CDPC15-22-28	15	28	22	26	4	48	13,78 €
CDPC15-22-36	15	36	22	26	4	61	20,00 €
CDPC16-26-16	16	16	26	30	4	45	12,34 €
CDPC16-26-28	16	28	26	30	4	76	16,14 €
CDPC16-26-36	16	36	26	30	4	97	22,09 €
CDPC16.1-26-16	16,1	16	26	30	4	45	17,62 €
CDPC16.1-26-28	16,1	28	26	30	4	76	21,84 €
CDPC16.1-26-36	16,1	36	26	30	4	96	28,59 €
CDPC16.5-26-16	16,5	16	26	30	4	44	12,34 €
CDPC16.5-26-28	16,5	28	26	30	4	73	16,14 €
CDPC16.5-26-36	16,5	36	26	30	4	93	21,91 €
CDPC17-26-16	17	16	26	30	4	42	12,34 €
CDPC17-26-28	17	28	26	30	4	70	16,14 €
CDPC17-26-36	17	36	26	30	4	90	21,91 €
CDPC18-26-16	18	16	26	30	4	39	12,34 €
CDPC18-26-28	18	28	26	30	4	64	16,14 €
CDPC18-26-36	18	36	26	30	4	82	21,91 €
CDPC19-30-20	19	20	30	34	5	71	16,14 €
CDPC19-30-36	19	36	30	34	5	125	21,45 €
CDPC19-30-45	19	45	30	34	5	154	32,16 €
CDPC20-30-20	20	20	30	34	5	67	16,14 €
CDPC20-30-36	20	36	30	34	5	0	21,45 €
CDPC20-30-45	20	45	30	34	5	143	32,16 €
CDPC20.1-30-20	20,1	20	30	34	5	66	21,45 €
CDPC20.1-30-36	20,1	36	30	34	5	115	28,09 €
CDPC20.1-30-45	20,1	45	30	34	5	142	41,09 €
CDPC22-30-20	22	20	30	34	5	56	16,14 €
CDPC22-30-36	22	36	30	34	5	97	21,45 €
CDPC22-30-45	22	45	30	34	5	120	32,16 €
CDPC25-35-20	25	20	35	39	5	80	20,72 €
CDPC25-35-36	25	36	35	39	5	138	25,49 €
CDPC25-35-45	25	45	35	39	5	171	37,98 €
CDPC30-42-25	30	25	42	46	5	139	30,94 €
CDPC30-42-45	30	45	42	46	5	245	36,65 €
CDPC30-42-56	30	56	42	46	5	304	55,88 €

*Depending on availability - Dimensions in mm