Straight clevis

For use with a male clevis

CLR
CLRss

- ***For attaching a gas spring***
- *Materials:*
  Steel
  316L stainless steel





Advantages

- *Allows gas springs to be mounted using a mounting plate and a* **CLM** *male clevis*

Accessories

- **CLM** *male clevis*
  (vol. 1 *p.179*)





DISCOUNTS

Qty	1+	6+	10+	15+	20+
Disc.	List	-10%	-15%	-20%	On request

Part number	A	B	C	E	F	ØG	H	J	ØD	ØT	N	L	R	Max load (N)	Stock*	Price each 1 to 5
Steel																
CLR-6	51	36	9,5	2,5	9	6,5	20	18	13	6	4,0	6,5	2,5	500	✔	17,80 €
CLR-8	51	36	9,5	2,5	9	6,5	20	18	13	8	4,0	13	2,5	1800	✔	17,80 €
Stainless steel																
CLR-6/SS	51	36	9,5	2,5	9	6,5	20	18	13	6	4,0	6,5	2,5	500	-	157,09 €
CLR-8/SS	51	36	9,5	2,5	9	6,5	20	18	13	8	4,0	13	2,5	1800	✔	144,00 €

**Depending on availability - Dimensions in mm*

Right angled mounting plate

SteSta stock

CNA
CNG

For ball joint or clevis

- ***For attaching a gas spring***
- *Materials:*
  Steel
  316L stainless steel

steel or stainless steel



CNA CNG


Advantages


- *Allows gas springs to be mounted by combining a mounting plate with a* ***RAS/IBJ*** *ball joint or a* ***CLM*** *clevis*

Accessories


- ***RAS*** *ball joint* **(vol. 1 p.175)** *or* ***CLM*** *clevis* **(vol. 1 p.179)**

NUOVO !





CNA
Use with a clevis



CNG
Use with a ball joint

IN STOCK*
Otherwise contact us

DISCOUNTS

Qty	1+	6+	10+	15+	20+
Disc.	List	-10%	-15%	-20%	On request

Use with a clevis

Part number Steel	Part number S/steel	A	B	C	E	F	ØG	H	J	K	ØT	N	P	Max load (N)	Price each 1 to 5 Steel	Price each 1 to 5 S/steel
CNA-4	-	19	16	3	1,5	4	3,4	10	5,75	4,25	4	3,5	4,5	180	15,80 €	-
CNA-6	CNA-6/SS	40	34	5	2	10	5,3	16	10	10	6	6,0	7	400	17,80 €	70,69 €
CNA-8	CNA-8/SS	40	34	5	2	10	5,3	16	10	10	8	7,0	11	1800	17,80 €	51,59 €

Use with a ball joint

Part number Steel	Part number S/steel	A	B	C	E	F	ØG	H	J	K	ØD	L	R	Max load (N)	Price each 1 to 5 Steel	Price each 1 to 5 S/steel
CNG-3,5	-	19	16	3	1,5	4	3,4	10	5,75	4,25	8	12,5	4,5	180	32,61 €	-
CNG-5	CNG-5/SS	40	34	5	2	10	5,3	16	10	10	8	13	5	400	17,80 €	72,67 €
CNG-8	CNG-8/SS	40	34	5	2	10	5,3	16	10	10	13	14,5	5	1800	18,42 €	72,67 €

**Depending on availability - Dimensions in mm*

Surface mounting plate

For ball joint or clevis

steel or stainless steel

COA
COG

- ***For attaching a gas spring***
- *Materials:*
  Steel
  316L stainless steel

Advantages

- *Allows gas springs to be mounted by combining a mounting plate with a* **RAS/IBJ** *ball joint or a* **CLM** *clevis*

Accessories

- **RAS** *ball joint* **(vol. 1 p.175)** *or* **CLM** *clevis* **(vol. 1 p.179)**





COA




COG

NUOVO !





COA
Use with a clevis



COG
Use with a ball joint

IN STOCK*
Otherwise contact us

DISCOUNTS

Qty	1+	6+	10+	15+	20+
Disc.	List	-10%	-15%	-20%	On request

Use with a clevis

Part number Steel	Part number S/steel	A	B	C	E	F	ØG	H	J	K	ØT	N	P	Max load (N)	Price each 1 to 5 Steel	Price each 1 to 5 S/steel
COA-4	-	18	13	1,5	5	5	4,3	16	1	2	4	4,5	4,5	180	18,57 €	-
COA-6	COA-6/SS	18	13	1,5	5	5	4,3	15,6	1	2,5	6	6,5	6,5	180	17,80 €	93,75 €
COA-8	COA-8/SS	55	23	3	7	10	5,3	30	2	5	8	10,0	11	1200	17,80 €	73,31 €

Use with a ball joint

Part number Steel	Part number S/steel	A	B	C	E	F	ØG	H	J	ØD	L	R	Max load (N)	Price each 1 to 5 Steel	Price each 1 to 5 S/steel
COG-3,5	-	18	13	1,5	5	5	4,3	16	1	8	13,5	5,5	180	17,41 €	-
COG-5	COG-5/SS	18	13	1,5	5	5	4,3	15,6	1	8	13,5	5,5	180	17,80 €	91,64 €
COG-8	COG-8/SS	55	23	3	7	10	5,3	30	2	13	17,5	8	1200	18,25 €	90,52 €

**Depending on availability - Dimensions in mm*