

# INDEX bolt with T handle


PITAss  
PITBss

Stainless steel - thermoplastic

- Indexing bolt with T-handle
- The T-handle allows a good grip for easy clamping with low effort.
- Materials:

303 stainless steel

T-handle : thermoplastic dark grey RAL7021  
or signal red RAL3020



## DISCOUNTS

Qty	1+	6+	20+
Disc.	List	-10%	On request

Part number	Colour	A	B	ØD	ØD1	L	L1	L2	L3	H	SW1	Spring force (N)		Price each 1 to 5
												Initial	Final	
<b>Shape A - No nut</b>														
PITA12-50/G/SS	Grey	50	15,5	6	M12x1,5	58	20	8	17	6	14	6	14	15,99 €
PITA16-60/G/SS	Grey	60	18,0	8	M16x1,5	77	26	10	23	8	19	15	35	21,21 €
PITA19-20/G/SS	Grey	72	19,0	10	M20x1,5	84	28	12	25	10	22	15	34	36,27 €
PITA12-50/R/SS	Red	50	15,5	6	M12x1,5	58	20	8	17	6	14	6	14	15,99 €
PITA16-60/R/SS	Red	60	18,0	8	M16x1,5	77	26	10	23	8	19	15	35	21,21 €
PITA19-20/R/SS	Red	72	19,0	10	M20x1,5	84	28	12	25	10	22	15	34	36,27 €
<b>Shape B - With nut</b>														
PITB12-50/G/SS	Grey	50	15,5	6	M12x1,5	58	20	8	17	6	14	6	14	17,60 €
PITB16-60/G/SS	Grey	60	18,0	8	M16x1,5	77	26	10	23	8	19	15	35	23,52 €
PITB19-20/G/SS	Grey	72	19,0	10	M20x1,5	84	28	12	25	10	22	15	34	38,83 €
PITB12-50/R/SS	Red	50	15,5	6	M12x1,5	58	20	8	17	6	14	6	14	17,60 €
PITB16-60/R/SS	Red	60	18,0	8	M16x1,5	77	26	10	23	8	19	15	35	23,52 €
PITB19-20/R/SS	Red	72	19,0	10	M20x1,5	84	28	12	25	10	22	15	34	38,83 €

All dimensions in mm