

Universal threaded lifting hook

Base rotates through 360°

RUD PPS



- **Universal lifting hook for all applications.**
- Suitable for use with cables, round or synthetic slings and chains
- Double ball bearings allows for loads to turn or tilt
- Visual overload indication on hook
- Hook and latched manufactured from forged steel and 100% crack tested
- Hook has a pink thermochromic finish (High visibility)

Option

- Can be supplied with a longer thread and nut for use with a through hole or for mounting on lighter metals such as aluminium

Info

- Conforms to EU Directive 98/37/CE
- Load capacity doesn't change with load direction



4 Suitable for lifting in any direction
Factor of safety = 4

CE

DISCOUNTS

Qty	1+	5+	10+	15+
Disc.	List -3%	-6%	On request	

Part number	Load		A	B	C	D	SW	F	G	E	Weight (kg)	Torque de serrage (Nm)	Price each	
	CMU (t)	ØM												
PPS-M12	0,63	M12	13	75	18	40	36	18	41	116	0,4	10	✓	137,17 €
PPS-M16	1,5	M16	20	97	25	46	41	24	50	146	0,9	30	✓	172,68 €
PPS-M20	2,5	M20	28	126	30	61	55	30	61	187	1,7	70	-	216,51 €
PPS-M24	4,0	M24	36	150	35	78	70	36	77	227	3,5	150	-	304,36 €
PPS-M30	5,0	M30	37	174	40	95	85	45	93	267	7,5	225	-	444,13 €
PPS-M36	8,0	M36	49	208	48	100	90	54	102	310	9,2	410	-	702,55 €

*Depending on availability - Dimensions in mm