

SteSta Pressed steel articulated foot Ø150

Accepts loads up to 40,000N

PTA150
PTA150ss

- **Levelling foot**
- Brilliant finish (Sand-blasted finish for base of the stainless steel version)
- Materials:


Steel version:

Base: Chromed steel sheet C40
Rod: Chromed steel (nut not supplied)
Sole: Vulcanised rubber NBR hardness 80° Shore

Stainless steel version:

Base: 304 stainless steel, brilliant or sand-blasted finish
Rod: 304 stainless steel (nut not supplied)
Sole: Vulcanised rubber NBR hardness 80° Shore

Sand-blasted stainless-steel version



Options

- Other rod sizes are available

DISCOUNTS

| | | | | | |
|-------|----------|------|------|-----|------------|
| Qty | 1+ | 15+ | 20+ | 25+ | 40+ |
| Disc. | List -5% | -10% | -15% | | On request |

| Part number | | ØD | ØF | B | A | A/F | G | H | Static load (N) | Price each 1 to 14 |
|-----------------------------|---------------------|-----|-----|-----|----|-----|----|-----|-----------------|--------------------|
| bright | sanded finish | | | | | | | | | |
| Steel foot | | | | | | | | | | |
| PTA150-24-100 | - | 150 | M24 | 100 | 44 | 24 | 35 | 144 | 40000 | 52.69 € |
| PTA150-24-150 | - | 150 | M24 | 150 | 44 | 24 | 35 | 194 | 40000 | 55.61 € |
| PTA150-24-200 | - | 150 | M24 | 200 | 44 | 24 | 35 | 244 | 40000 | 58.77 € |
| PTA150-24-250 | - | 150 | M24 | 250 | 44 | 24 | 35 | 294 | 40000 | 61.72 € |
| PTA150-30-100 | - | 150 | M30 | 100 | 44 | 30 | 35 | 145 | 40000 | 57.84 € |
| PTA150-30-150 | - | 150 | M30 | 150 | 44 | 30 | 35 | 195 | 40000 | 59.65 € |
| PTA150-30-200 | - | 150 | M30 | 200 | 44 | 30 | 35 | 245 | 40000 | 65.66 € |
| PTA150-30-250 | - | 150 | M30 | 250 | 44 | 30 | 35 | 295 | 40000 | 73.95 € |
| Stainless steel foot | | | | | | | | | | |
| PTA150-24-100/SS | PTA150-24-100/SS/SB | 150 | M24 | 100 | 49 | 20 | 35 | 149 | 40000 | 72.32 € |
| PTA150-24-150/SS | PTA150-24-150/SS/SB | 150 | M24 | 150 | 49 | 20 | 35 | 199 | 40000 | 76.29 € |
| PTA150-24-200/SS | PTA150-24-200/SS/SB | 150 | M24 | 200 | 49 | 20 | 35 | 249 | 40000 | 80.27 € |
| PTA150-24-250/SS | PTA150-24-250/SS/SB | 150 | M24 | 250 | 49 | 20 | 35 | 299 | 40000 | 84.26 € |
| PTA150-30-100/SS | PTA150-30-100/SS/SB | 150 | M30 | 100 | 50 | 26 | 35 | 150 | 40000 | 82.29 € |
| PTA150-30-150/SS | PTA150-30-150/SS/SB | 150 | M30 | 150 | 50 | 26 | 35 | 200 | 40000 | 88.11 € |
| PTA150-30-200/SS | PTA150-30-200/SS/SB | 150 | M30 | 200 | 50 | 26 | 35 | 250 | 40000 | 93.00 € |
| PTA150-30-250/SS | PTA150-30-250/SS/SB | 150 | M30 | 250 | 50 | 26 | 35 | 300 | 40000 | 97.86 € |

All dimensions in mm

Fax **0 825 88 6000**
Service 0,15 €/min
+ prix appel

cial2@hpceurope.com

HPC SUPPLEMENT 2019