

Articulated foot with sheet metal base Ø50

Max load: 4000N
Rubber sole in EPDM, blue

- **Articulated adjustable levelling feet**
- Axial articulation +/- 10°
- With non-slip sole in EPDM Blue
- Stainless steel in shiny finish
- Materials:
 - Base: shiny 304 stainless steel sheet
 - Thread: 304 stainless steel, supplied without nut
 - Sole: EPDM blue

Food industry

Sole in EPDM, blue




Options

- Other thread dimensions on request
- 316 grade Stainless steel on request

Advantages

- Hygienic special sole for easy cleaning.
- Food processing, Pharmaceutical and Chemical Environment



DISCOUNTS

Qty	1+	6+	10+	15+	20+
Disc.	Price	-5%	-10%	-15%	On request


References	ØD	ØF	B	A	A/F	G	H	Static load(N)	Price per unit 1 to 5
PTA50-10-75/SS/EB	50	M10	75	29	14	19	104	4,000	17,56€
PTA50-10-125/SS/EB	50	M10	125	29	14	19	154	4,000	19,83€
PTA50-12-75/SS/EB	50	M12	75	29	14	19	104	4,000	17,56€
PTA50-12-125/SS/EB	50	M12	125	29	14	19	154	4,000	19,83€
PTA50-16-75/SS/EB	50	M16	75	34	13	19	109	4,000	20,38€
PTA50-16-100/SS/EB	50	M16	100	34	13	19	134	4,000	21,14€
PTA50-16-150/SS/EB	50	M16	150	34	13	19	184	4,000	23,13€

* Depending on availability - Dimensions in mm


Our other products



RTN
Bowex ®, toothed,
Nylon



TPR
High helix leadscrew,
Leadscrew only - up
to 40mm per rotation



B
Bevel gear - Steel
60C40, 1:1



BPM_LOK
Slotted spring plunger
with ball tip, LONG-
LOK - Steel



BRI
Panels accessories,
Panel holder



PWDL_PWGDL2
Worm - precision
range, Delrin



PBG
Bevel gear - precision
range, 1:1



HTD8M_20
HTD-type pulley for
RPP-type belt, HTD8
Cast



CHT90
3 phase AC
asynchronous motor,
1.1 to 1.85kW



BABss
Ball pin, 303 Stainless
steel



BLHB20
Right angled gearbox,
up to 1.77 Nm



PTKss
Foot for the food
industry, Stainless
steel - 3-A standard

Complementary products



PTA80ssEB
Articulated foot with
sheet metal base,
Articulated foot



PTA100ssEB
Articulated foot with
sheet metal base,
Articulated foot



PAMF80EB
Articulated foot with
sheet metal base,
Articulated foot



PAMF100EB
Articulated foot with
sheet metal base,
Articulated foot