


# Single row cylindrical roller bearings New

## QNUP

### One fixed internal flange and one free internal flange

- The external ring has two fixed flanges whereas the internal ring has one fixed and one free flange.
- The axial movement of the shaft is restricted in both directions.
- Static and dynamic loads are radial loads
- Max working temperature: Polyamide cage: 120°C  
Steel or brass cage: 150°C
- Materials:
  - Steel flanges and cylinders
  - P: polyamide cage
  - M: solid brass cage
  - J: pressed steel cage



### DISCOUNTS

Qty	1+	6+	20+	40+	60+
Disc.	List -10%	-15%	-20%	On request	

Part number	Ød	ØD1	B	Load (kN)		Speed (rpm)		Weight (kg)	Price each 1 to 5
				Dynamic (C)	Static (Co)	lubricant	Oil		
QNUP203-M	17	40	12	17	14	16830	19800	0,073	14,94 €
QNUP2203-P	17	40	16	23	21	16830	19800	0,097	25,00 €
QNUP204-P	20	47	14	25	22	14535	17100	0,12	15,65 €
QNUP205-J	25	52	15	28	26	12240	14400	0,14	17,43 €
QNUP2205-M	25	52	18	33	33	12240	14400	0,17	26,54 €
QNUP206-P	30	62	16	43	36	10710	12600	0,22	21,43 €
QNUP2206-J	30	62	20	54	48	10710	12600	0,27	28,91 €
QNUP207-J	35	72	17	55	47	9180	10800	0,32	22,76 €
QNUP2207-P	35	72	23	68	62	9180	10800	0,42	30,33 €
QNUP307-J	35	80	21	74	62	8415	9900	0,51	28,65 €
QNUP2307-J	35	80	31	104	96	8415	9900	0,75	43,56 €
QNUP208-J	40	80	18	61	52	8415	9900	0,4	29,29 €
QNUP2308-J	40	90	33	126	118	7268	8550	0,98	53,07 €
QNUP209-J	45	85	19	68	63	7268	8550	0,45	30,65 €
QNUP210-P	50	90	20	72	68	6885	8100	0,51	31,33 €
QNUP2310-J	50	110	40	182	182	6120	7200	1,8	74,06 €
QNUP211-J	55	100	21	95	93	6120	7200	0,69	34,86 €
QNUP311-P	55	120	29	153	140	5355	6300	1,55	53,75 €
QNUP212-J	60	110	22	106	100	5738	6750	0,86	41,00 €
QNUP213-M	65	120	23	120	116	5126	6030	1,1	47,15 €

Dimensions in mm