

Rigging screw with 2 jaws **stainless steel** **New** **Sta**

RDCss

Diameter M5 to M20


Rigging screw with 2 welded jaws

- Material : Stainless steel 316
- Supplied with fitted locking nuts

Application

The breaking strength is obtained by multiplying the SWL by a factor of safety of 4

NEW!



DISCOUNTS

Qty	1+	6+	20+	50+
Disc.	List	-10%	-20%	On request

Part number	Diameter	ØC	B	E	L1	L2	SWL (kg)	Weight (kg)	Price each 1 to 5
RDC-5/SS	5	5	10	8	126	190	150	0,056	15,45 €
RDC-6/SS	6	6	10	7,7	136	211	250	0,076	17,18 €
RDC-8/SS	8	8	11	9,4	170	255	360	0,154	24,20 €
RDC-10/SS	10	10	14,7	13,5	195	280	500	0,26	31,19 €
RDC-12/SS	12	12	15	22	260	380	650	0,536	43,05 €
RDC-14/SS	14	14	15	23	300	430	790	0,72	56,15 €
RDC-16/SS	16	16	21	24	315	455	980	1,086	80,89 €
RDC-20/SS	20	20	28	38	410	560	1300	2,124	119,88 €