Polyamide wheel

For loads up to 600kg

RPC

- ***Light coloured Polyamide wheel***
- *Smooth central bore*
- *Working temperature range: -30°C to +80°C*



Advantages

- *Shock and abrasion resistant*
- *Does not stain floors*
- *Does not mark floors*
- *Resists most chemical agents*
- *Low rolling resistance*
- *For solid and hard floors*
- *Ideal for use in wet and dirty environments (fish markets, butcher shops, canneries)*

For smooth surfaces



DISCOUNTS

Qty	1+	10+	30+
Disc.	List	-5%	On request


Part number	ØD	B	C	ØA	Maximum load (kg)	Stock*	Price each 1 to 9
RPC60-31/ML	60	31	40	12	200	✔	2,50 €
RPC80-32/ML	80	32	40	12	250	✔	2,72 €
RPC100-32/ML	100	32	40	12	300	✔	3,77 €
RPC100-35/ML	100	35	48	15	350	-	11,29 €
RPC125-36/ML	125	36	50	15	350	-	6,88 €
RPC125-41/ML	125	41	59	20	400	-	13,27 €
RPC150-37/ML	150	37	49	15	400	-	9,96 €
RPC160-40/ML	160	40	58	20	500	-	27,31 €
RPC200-50/ML	200	50	58	20	600	-	29,65 €

**Depending on availability -Dimensions in mm*

Polyamide castor with mounting plate

RPCPL — For heavy loads up to 600kg

- ***Industrial wheel suitable for loads up to 600kg***
- *Swivel system uses two ball races*
- *Swivel castor with double locks: simple to lock/unlock using foot operated pedal*
- *Smooth central bore*
- *Materials:*
  Top plate: pressed steel sheet, protected by bright zinc plating
  Polyamide wheel **RPC (tome 5 p.51)**
- *Working temperature range: - 30°C to + 80°C*



Fixed



Swivel



Swivel with double brake

Advantages

- *Light*
- *Will not mark or stain floor*
- *Low rolling resistance*
- *For solid, hard floors*



ØD



B



H



L



M



ØT



ØK

DISCOUNTS

Qty	1+	10+	30+
Disc.	List	-5%	On request

Part number	ØD	B	H	L	M	ØT	Swivel interference ØK	Max. load (kg)	Stock*	Price each 1 to 9
Fixed										
RPC60/PL/F	60	30	100	110x85	80x60	8	-	200	-	8,25 €
RPC80/PL/F	80	32	109	110x85	80x60	8	-	250	✔	8,06 €
RPC100/PL/F	100	32	126	110x85	80x60	8	-	300	✔	8,34 €
RPC125/PL/F	125	36	154	110x85	80x60	8	-	350	-	13,47 €
RPC150/PL/F	150	37	182	110x85	80x60	8	-	400	-	18,38 €
RPC160/PL/F	160	40	196	135x110	105x80	11	-	500	-	32,06 €
RPC200/PL/F	200	50	241	135x110	105x80	11	-	600	-	37,99 €
Swivel										
RPC60/PL/P	60	30	100	110x85	80x60	8	140	200	-	11,43 €
RPC80/PL/P	80	32	109	110x85	80x60	8	160	250	✔	9,48 €
RPC100/PL/P	100	32	126	110x85	80x60	8	184	300	✔	9,72 €
RPC125/PL/P	125	36	154	110x85	80x60	8	210	350	-	14,45 €
RPC150/PL/P	150	37	182	110x85	80x60	8	246	400	-	23,01 €
RPC160/PL/P	160	40	196	135x110	105x80	11	268	500	-	35,54 €
RPC200/PL/P	200	50	241	135x110	105x80	11	318	600	-	40,63 €
Swivel with double brake										
RPC80/PL/PDB	80	32	109	110x85	80x60	8	290	250	✔	12,49 €
RPC100/PL/PDB	100	32	126	110x85	80x60	8	290	300	✔	13,41 €
RPC125/PL/PDB	125	36	154	110x85	80x60	8	290	350	✔	18,60 €
RPC150/PL/PDB	150	37	182	110x85	80x60	8	290	400	-	27,97 €
RPC160/PL/PDB	160	40	196	135x110	105x80	11	268	500	-	39,76 €
RPC200/PL/PDB	200	50	241	135x110	105x80	11	318	600	-	45,49 €

**Depending on availability - Dimensions in mm*

Stock Polyamide castor with central hole

For heavy loads up to 600kg — RPCTC

- ***Industrial wheel suitable for loads up to 600kg***
- *Swivel system uses two ball races*
- *Swivel castor with double locks:*
  simple to lock/unlock using foot operated pedal
- *Smooth central bore*
- *Materials:*
  Top plate: pressed steel sheet, protected by bright zinc plating
  Polyamide wheel **RPC (tome 5 p.51)**
- *Working temperature range: - 30°C to + 80°C*




Swivel



Swivel with double brake

Advantages

- *Light*
- *Will not mark or stain floor*
- *Low rolling resistance*
- *For solid, hard floors*



DISCOUNTS

Qty	1+	10+	30+
Disc.	List	-5%	On request

Part number	ØD	B	H	ØE	Swivel interference ØK	Max load (kg)	Stock*	Price each 1 to 9
Swivel								
RPC60/TC/P	60	30	97	12	140	200	-	11,12 €
RPC80/TC/P	80	32	106	12	160	250	✔	12,04 €
RPC100/TC/P	100	32	124	12	184	300	✔	12,96 €
RPC125/TC/P	125	36	152	12	210	350	-	17,57 €
RPC150/TC/P	150	37	181	12	246	400	-	24,69 €
RPC160/TC/P	160	40	189	12,5	268	500	-	49,94 €
RPC200/TC/P	200	50	232	12,5	318	600	-	57,40 €
Swivel with double brake								
RPC80/TC/PDB	80	32	106	12	290	250	✔	17,79 €
RPC100/TC/PDB	100	32	124	12	290	300	✔	18,67 €
RPC125/TC/PDB	125	36	152	12	290	350	-	23,74 €
RPC150/TC/PDB	150	37	181	12	290	400	-	31,19 €
RPC160/TC/PDB	160	40	189	12,5	268	500	-	62,99 €
RPC200/TC/PDB	200	50	232	12,5	318	600	-	65,35 €

**Depending on availability - Dimensions in mm*

Polyamide castor with mounting plate stainless steel

Stock*

RPCPLSS

For heavy loads up to 600kg

- ***Industrial wheel suitable for loads up to 600kg***
- *Swivel system uses two ball races*
- *Swivel castor with double locks: simple to lock/unlock using foot operated pedal*
- *Smooth central bore*
- *Materials:*
  Top plate: pressed stainless steel sheet
  Polyamide wheel **RPC (tome 5 p.51)**
- *Working temperature range: - 30°C to + 80°C*



Fixed




Swivel



Swivel with double brake

Advantages

- *Light*
- *Will not mark or stain floor*
- *Low rolling resistance*
- *For solid, hard floors*
- *Ideal for use in wet and dirty environments (fish markets, butcher shops, canneries)*



DISCOUNTS

Qty	1+	5+	15+
Disc.	List	-5%	On request

Part number	ØD	B	H	L	M	ØT	Swivel interference ØK	Max load (kg)	Stock*	Price each 1 to 4
Fixed										
RPC60/PL/F/SS	60	31	96	115x83	80x60	11x9	-	200	-	20,52 €
RPC80/PL/F/SS	80	32	105	115x83	80x60	11x9	-	250	✔	21,50 €
RPC100/PL/F/SS	100	32	124	115x83	80x60	11x9	-	300	✔	22,00 €
RPC125/PL/F/SS	125	36	152	115x83	80x60	11x9	-	350	-	29,35 €
RPC150/PL/F/SS	150	37	179	115x83	80x60	11x9	-	400	-	57,46 €
RPC160/PL/F/SS	160	40	197	135x105	105x80	11	-	600	-	79,45 €
RPC200/PL/F/SS	200	50	240	135x105	105x80	11	-	700	-	84,60 €
Swivel										
RPC60/PL/P/SS	60	31	96	115x83	80x60	11x9	155	200	-	30,61 €
RPC80/PL/P/SS	80	32	105	115x83	80x60	11x9	173	250	✔	30,54 €
RPC100/PL/P/SS	100	32	124	115x83	80x60	11x9	193	300	✔	32,77 €
RPC125/PL/P/SS	125	36	152	115x83	80x60	11x9	221	350	-	38,23 €
RPC150/PL/P/SS	150	37	179	115x83	80x60	11x9	257	400	-	77,85 €
RPC160/PL/P/SS	160	40	197	135x105	105x80	11	268	600	-	89,60 €
RPC200/PL/P/SS	200	50	240	135x105	105x80	11	318	700	-	96,15 €
Swivel with double brake										
RPC80/PL/PDB/SS	80	32	105	115x83	80x60	11x9	293	250	✔	39,86 €
RPC100/PL/PDB/SS	100	32	124	115x83	80x60	11x9	293	300	✔	42,01 €
RPC125/PL/PDB/SS	125	36	152	115x83	80x60	11x9	293	350	-	49,28 €
RPC150/PL/PDB/SS	150	37	179	115x83	80x60	11x9	293	400	-	100,19 €
RPC160/PL/PDB/SS	160	40	197	135x105	105x80	11	268	600	-	108,90 €
RPC200/PL/PDB/SS	200	50	240	135x105	105x80	11	318	700	-	121,62 €

**Depending on availability -Dimensions in mm*

Polyamide castor with central hole, stainless steel

RPCTCSS — For heavy loads up to 600kg

- ***Industrial wheel suitable for loads up to 600kg***
- *Swivel system uses two ball races*
- *Swivel castor with double locks:*
  simple to lock/unlock using foot operated pedal
- *Smooth central bore*
- *Materials:*
  Top plate: pressed stainless steel sheet
  Polyamide wheel **RPC (tome 5 p.51)**
- *Working temperature range:* - 30°C to + 80°C



Swivel



Swivel with double brake

Advantages

- *Light*
- *Will not mark or stain floor*
- *Low rolling resistance*
- *For solid, hard floors*
- *Ideal for use in wet and dirty environments (fish markets, butcher shops, canneries)*



DISCOUNTS

Qty	1+	5+	15+
Disc.	List	-5%	On request

Part number	ØD	B	H	ØE	Swivel interference ØK	Max load (kg)	Price each 1 to 4
Swivel							
RPC60/TC/P/SS	60	31	96	12	155	200	29,15 €
RPC80/TC/P/SS	80	32	109	12	173	250	30,54 €
RPC100/TC/P/SS	100	32	124	12	193	300	31,21 €
RPC125/TC/P/SS	125	36	152	12	221	350	38,23 €
RPC150/TC/P/SS	150	37	179	12	257	400	77,85 €
RPC160/TC/P/SS	160	40	197	16	268	600	88,20 €
RPC200/TC/P/SS	200	50	240	16	318	700	94,03 €
Swivel with double brake							
RPC80/TC/PDB/SS	80	32	109	12	173	250	39,86 €
RPC100/TC/PDB/SS	100	32	124	12	193	300	42,01 €
RPC125/TC/PDB/SS	125	36	152	12	221	350	49,28 €
RPC150/TC/PDB/SS	150	37	179	12	257	400	100,19 €
RPC160/TC/PDB/SS	160	40	197	16	268	600	107,58 €
RPC200/TC/PDB/SS	200	50	240	16	318	700	120,27 €

Dimensions in mm