
Locking assembly not self-centering Ste Stock ★★★


RTT Medium/high torque

NUOVO !

- ***Inserts between the shaft and the bore***
- *High transmissible torque*
- *Contact pressure spread evenly*
- *Easy to assemble and dismantle*
- *Reduced width*
- *Backlash free*
- ***No constraints due to keyway***
- *Increases the resistant part of the section of the shaft*
- *Suitable for alternating rotational movements*
- *Up to 4 units can be used together*
- *Materials:*
  Body: steel
  Screws: steel DIN 912 12.9







Options

- *Other diameters available (up to 220mm bore)*
- *Stainless steel version*

Info.

- ***Pn: hub surface pressure*
- ***Pw: shaft surface pressure*

DISCOUNTS

Qty	1+	6+	20+	40+	60+	100+
Disc.	List	-10%	-15%	-20%	-25%	On request


Part number	ØA	ØD	L	H	Screw M	Tightening torque TA(Nm)	Transmissible torque T (Nm)	**Pw (N/mm²)	**Pn (N/mm²)	Stock*	Price each 1 to 5
RTT20-47	20	47	20	28	8xM6x18	14	270	210	90	✔	16,30 €
RTT22-47	22	47	20	28	8xM6x18	14	300	195	90	✔	16,30 €
RTT24-50	24	50	20	28	9xM6x18	14	360	195	95	✔	16,82 €
RTT25-50	25	50	20	28	9xM6x18	14	380	190	85	✔	16,82 €
RTT28-55	28	55	20	28	10xM6x18	14	500	187	96	-	18,77 €
RTT30-55	30	55	20	28	10xM6x18	14	530	176	96	✔	20,39 €
RTT32-60	32	60	20	28	12xM6x18	14	630	192	105	-	20,62 €
RTT35-60	35	60	20	28	12xM6x18	14	700	180	105	-	20,69 €
RTT38-65	38	65	20	28	14xM6x18	14	860	183	107	-	22,71 €
RTT40-65	40	65	20	28	14xM6x18	14	910	180	110	✔	22,99 €
RTT42-75	42	75	24	34	12xM8x22	35	1500	226	125	-	28,34 €
RTT45-75	45	75	24	34	12xM8x22	35	1610	210	125	-	28,61 €
RTT48-80	48	80	24	34	12xM8x22	35	1700	196	115	-	29,88 €
RTT50-80	50	80	24	34	12xM8x22	35	1770	190	115	✔	29,92 €
RTT55-85	55	85	24	34	14xM8x22	35	2270	200	130	-	32,91 €
RTT60-90	60	90	24	34	14xM8x22	35	2470	180	120	✔	34,73 €
RTT65-95	65	95	24	34	16xM8x22	35	3040	190	130	-	37,80 €
RTT70-110	70	110	28	40	14xM10x25	70	4600	210	130	-	49,71 €
RTT75-115	75	115	28	40	14xM10x25	70	4900	195	125	-	53,85 €
RTT80-120	80	120	28	40	14xM10x25	70	5200	180	120	-	56,80 €
RTT85-125	85	125	28	40	16xM10x25	70	6300	195	130	-	60,46 €
RTT90-130	90	130	28	40	16xM10x25	70	6600	180	125	-	59,80 €
RTT95-135	95	135	28	40	18xM10x25	70	7900	195	135	-	66,72 €
RTT100-145	100	145	33	47	14xM12x30	125	9600	195	135	-	79,32 €

**Depending on availability - Dimensions in mm*

Sta New ★★★ Stainless steel locking assembly

Medium/high torque - not self-centering RTTss


- ***Inserts between the shaft and the bore***
- *High transmissible torque*
- *Contact pressure spread evenly*
- *Easy to assembly and dismantle*
- *Reduced width*
- *Backlash free*
- ***No constraints due to keyway***
- *Increases the resistant part of the shaft*
- *Suitable for alternating movement*
- *Up to 4 units can be used together*
- *Material*
  Stainless steel






Info.

- **P_N : *hub surface pressure*
- **P_W : *shaft surface pressure*





REMISES

Qty	1+	2+	5+
Disc.	List	-5%	On request


Part number	ØA	ØD	L1	L	L2	Screw M	Tightening torque TA (Nm)	Transmissible torque T (Nm)	**Pw (N/mm²)	**PN (N/mm²)	Stock*	Price each
RTT20-47/SS	20	47	26	20	17	8xM6x18	8	110	133	57	✔	43,75 €
RTT22-47/SS	22	47	26	20	17	8xM6x18	8	120	131	57	-	Su richiesta
RTT24-50/SS	24	50	26	20	17	9xM6x18	8	150	125	60	✔	45,71 €
RTT25-50/SS	25	50	26	20	17	9xM6x18	8	155	120	60	✔	44,99 €
RTT28-55/SS	28	55	26	20	17	9xM6x18	8	170	107	55	✔	48,15 €
RTT30-55/SS	30	55	26	20	17	9xM6x18	8	185	100	55	✔	49,60 €
RTT32-60/SS	32	60	26	20	17	12xM6x18	8	265	125	66	-	51,80 €
RTT35-60/SS	35	60	26	20	17	12xM6x18	8	290	114	67	-	51,89 €
RTT38-65/SS	38	65	26	20	17	15xM6x18	8	390	131	77	-	59,86 €
RTT40-65/SS	40	65	26	20	17	15xM6x18	8	410	125	77	-	67,34 €
RTT42-75/SS	42	75	32	24	20	12xM8x22	18	595	138	78	-	77,18 €
RTT45-75/SS	45	75	32	24	20	12xM8x22	18	635	129	78	-	81,18 €
RTT48-80/SS	48	80	32	24	20	12xM8x22	18	680	121	73	-	85,33 €
RTT50-80/SS	50	80	32	24	20	12xM8x22	18	700	116	73	-	91,28 €

**Depending on availabiliity - Dimensions in mm*


Self-centering flanged locking assembly Ste Stock ★★★


RT25 Medium/high torque

- ***Inserts between the shaft and the bore***
- *High transmissible torque*
- *Contact pressure spread evenly*
- *Easy to assembly and dismantle*
- *Reduced width*
- *Backlash free*
- ***No constraints due to keyway***
- *Increases the resistant part of the section of the shaft*
- *Suitable for alternating rotational movements*









Options

- *Other diameters available (up to 100mm bore)*

Info.

- ** PN: hub surface pressure*
- ** Pw: shaft surface pressure*

DISCOUNTS

Qty.	1+	6+	10+	20+	40+	60+
Disc.	List	-20%	-30%	-40%	-50%	On request

Part number	ØA	ØG	ØD	L	Screw M	K	Tightening torque TA(Nm)	Transmissible torque T (Nm)	*Pw (N/mm²)	*PN (N/mm²)	Stock*	Price each 1 to 5
RT25-6-14	6	14	25	22,5	3xM3x10	10,0	2,2	12	190	80	✔	26,82 €
RT25-8-15	8	15	27	25,5	3xM4x12	12,0	5,0	29	205	110	✔	23,30 €
RT25-9-16	9	16	28	27,5	3xM4x12	14,0	5,0	31	150	85	✔	23,50 €
RT25-10-16	10	16	28	27,5	3xM4x12	14,0	5,0	35	140	85	✔	23,65 €
RT25-11-18	11	18	32	27,5	4xM4x12	14,0	5,0	52	170	105	✔	23,60 €
RT25-12-18	12	18	32	27,5	4xM4x12	14,0	5,0	58	150	100	✔	23,59 €
RT25-14-23	14	23	39	27,5	4xM4x12	14,0	5,0	69	140	80	✔	21,19 €
RT25-16-24	16	24	45	36,5	4xM6x12	16,0	17,0	180	148	98	✔	23,95 €
RT25-18-26	18	26	47	39,5	4xM6x18	19,0	17,0	200	180	125	✔	24,44 €
RT25-19-27	19	27	49	39,5	4xM6x18	19,0	17,0	210	170	120	✔	24,28 €
RT25-20-28	20	28	50	39,5	4xM6x18	19,0	17,0	220	160	115	✔	24,63 €
RT25-22-32	22	32	54	46,5	4xM6x18	26,0	17,0	250	115	80	✔	26,74 €
RT25-24-34	24	34	56	46,5	6xM6x18	26,0	17,0	395	146	102	✔	26,81 €
RT25-25-34	25	34	56	46,5	6xM6x18	26,0	17,0	410	140	102	✔	27,48 €
RT25-28-39	28	39	61	46,5	6xM6x18	25,5	17,0	465	135	98	✔	30,45 €
RT25-30-41	30	41	62	46,5	6xM6x18	25,5	17,0	510	127	90	✔	31,17 €
RT25-32-43	32	43	65	46,5	8xM6x18	25,5	17,0	705	146	108	✔	33,99 €
RT25-35-47	35	47	69	52,5	8xM6x18	31,5	17,0	790	105	80	-	34,78 €
RT25-38-50	38	50	72	52,5	8xM6x18	31,5	17,0	860	100	76	✔	38,83 €
RT25-40-53	40	53	75	52,5	8xM6x18	31,5	17,0	900	96	72	✔	41,10 €
RT25-42-55	42	55	78	52,5	8xM6x18	31,5	17,0	940	90	70	-	45,34 €
RT25-45-59	45	59	86	71,0	8xM8x22	45,0	41,0	1840	110	85	-	61,31 €
RT25-48-62	48	62	87	71,0	8xM8x22	45,0	41,0	2000	105	80	-	65,86 €
RT25-50-65	50	65	92	71,0	8xM8x22	45,0	41,0	2100	100	75	-	72,01 €
RT25-55-71	55	71	98	81,0	9xM8x22	55,0	41,0	2580	85	65	-	85,72 €

**Depending on availabiliity - Dimensions in mm*

Sta ★★★ Stainless steel self-centering flanged locking assembly


Medium/high torque RT25ss


NUOVO !



Stainless steel

- ***Inserts between the shaft and the bore***
- *High transmissible torque*
- *Contact pressure spread evenly*
- *Easy to assembly and dismantle*
- *Reduced width*
- *Backlash free*
- ***No constraints due to keyway***
- *Increases the resistant part of the shaft*
- *Suitable for alternating rotational movement*
- *Material*
  Stainless steel





Info.

- **P_N : *hub surface pressure*
- **P_W : *shaft surface pressure*

DISCOUNTS

Qty	1+	2+	5+
Disc.	List	-5%	On request

Part number	ØA	ØG	ØD	L1	L	K	Screw M	Tightening torque TA (Nm)	Transmissible torque T (Nm)	**Pw (N/mm²)	**PN (N/mm²)	Stock*	Price each
RT25-10-16/SS	10	16	29	31	27	14	4xM4x12	2	22	82	51	✔	27,48 €
RT25-12-18/SS	12	18	32	32	28	14	4xM4x12	2	26	69	46	✔	28,73 €
RT25-14-23/SS	14	23	38	32	28	14	4xM4x12	2	30	59	36	-	31,92 €
RT25-15-24/SS	15	24	44	43	37	16	4xM6x18	8	73	107	67	-	44,12 €
RT25-16-24/SS	16	24	44	43	37	16	4xM6x18	8	78	101	67	✔	44,18 €
RT25-18-26/SS	18	26	47	45	39	18	4xM6x18	8	87	79	55	-	44,01 €
RT25-19-27/SS	19	27	49	45	39	18	4xM6x18	8	92	75	53	-	44,55 €
RT25-20-28/SS	20	28	50	45	39	18	4xM6x18	8	97	71	51	✔	47,98 €
RT25-22-32/SS	22	32	54	52	46	25	4xM6x18	8	105	47	32	-	53,68 €
RT25-24-34/SS	24	34	56	52	46	25	6xM6x18	8	175	64	45	✔	62,23 €
RT25-25-34/SS	25	34	56	52	46	25	6xM6x18	8	180	62	45	✔	61,52 €
RT25-28-39/SS	28	39	61	52	46	25	6xM6x18	8	200	55	40	-	66,58 €
RT25-30-41/SS	30	41	62	52	46	25	6xM6x18	8	220	51	38	✔	74,89 €
RT25-32-43/SS	32	43	65	52	46	25	8xM6x18	8	310	64	48	-	80,69 €
RT25-35-47/SS	35	47	66	59	53	32	8xM6x18	8	340	46	34	✔	85,93 €
RT25-38-50/SS	38	50	72	59	53	32	8xM6x18	8	370	42	32	-	93,10 €
RT25-40-53/SS	40	53	75	59	53	32	8xM6x18	8	390	40	30	-	110,45 €
RT25-42-55/SS	42	55	78	59	53	32	8xM6x18	8	410	39	29	-	115,39 €
RT25-45-59/SS	45	59	86	78	70	45	8xM8x22	18	820	48	36	-	161,44 €
RT25-48-62/SS	48	62	87	78	70	45	8xM8x22	18	880	45	35	-	165,97 €
RT25-50-65/SS	50	65	92	78	70	45	8xM8x22	18	910	43	33	-	199,73 €

**Depending on availabiliity - Dimensions in mm*


Self-centering locking assembly

Stock Ste

RT61

Torque medium/low


- ***Inserts between the shaft and the bore***
- *Contact pressure spread evenly*
- *Easy to assembly and dismantle*
- *Reduced width*
- *Backlash free*
- ***No constraints due to keyway***
- *Increases the resistant part of the shaft*
- *Suitable for alternating rotational movement*
- *Material*
  Steel C45E



NUOVO !

Info.

- ***PN: hub surface pressure*
- ***PW: shaft surface pressure*



DISCOUNT

Qty	1+	6+	20+	40+	60+	100+
Disc.	List	-10%	-15%	-20%	-25%	On request

Part number	ØA	ØG	L	L1	Screw M	Tightening torque TA (Nm)	Transmissible torque T (Nm)	PW** (N/mm²)	PN* (N/mm²)	Stock*	Price each 1 to 5
RT61-10-20	10	20	15,5	13	4xM2,5x12	1,2	19	89	45	✔	7,48 €
RT61-12-22	12	22	15,5	13	4xM2,5x12	1,2	23	75	41	✔	7,74 €
RT61-14-26	14	26	20,0	17	4xM3x16	2,1	39	71	38	-	8,19 €
RT61-15-28	15	28	20,0	17	4xM3x16	2,1	42	66	35	-	8,19 €
RT61-16-32	16	32	21,0	17	4xM4x16	4,9	77	107	54	✔	9,17 €
RT61-18-35	18	35	25,0	21	4xM4x20	4,9	87	77	40	✔	9,49 €
RT61-19-35	19	35	25,0	21	4xM4x20	4,9	91	73	40	-	9,49 €
RT61-20-38	20	38	26,0	21	4xM5x20	10,0	157	113	60	✔	9,83 €
RT61-22-40	22	40	26,0	21	4xM5x20	10,0	173	103	57	✔	11,18 €
RT61-24-47	24	47	32,0	26	4xM6x24	17,0	268	110	56	-	13,08 €
RT61-25-47	25	47	32,0	26	4xM6x24	17,0	279	105	56	✔	13,27 €

**Depending on availability - Dimensions in mm*


Sta Stock Stainless steel self-centering locking assembly

Torque medium/low

RT61ss

- **Inserts between the shaft and the bore**
- Contact pressure spread evenly
- Easy to assembly and dismantle
- Reduced width
- Backlash free
- **No constraints due to keyway**
- Increases the resistant part of the shaft
- Suitable for alternating rotational movement
- Material
  Stainless steel


stainless steel



NUOVO !

Info.

- **Pn: hub surface pressure
- **Pw: shaft surface pressure



DISCOUNT

Qty	1+	2+	5+
Disc.	List	-5%	On request


Part number	ØA	ØG	L	L1	Screw M	Tightening torque TA (Nm)	Transmissible torque T (Nm)	Pw** (N/mm²)	Pn* (N/mm²)	Stock*	Price each
RT61-10-20/SS	10	20	15,5	13	4xM2,5x12	0,5	6	33	17	✔	20,53 €
RT61-12-22/SS	12	22	15,5	13	4xM2,5x12	0,5	7	26	15	✔	20,79 €
RT61-14-26/SS	14	26	20,0	17	4xM3x16	0,9	13	28	15	-	22,24 €
RT61-15-28/SS	15	28	20,0	17	4xM3x16	0,9	14	26	14	-	22,66 €
RT61-16-32/SS	16	32	21,0	17	4xM4x16	2,2	28	45	23	✔	23,96 €
RT61-18-35/SS	18	35	25,0	21	4xM4x20	2,2	32	32	17	-	Su richiesta
RT61-19-35/SS	19	35	25,0	21	4xM4x20	2,2	34	31	17	-	26,09 €
RT61-20-38/SS	20	38	26,0	21	4xM5x20	4,2	55	45	24	✔	28,01 €
RT61-22-40/SS	22	40	26,0	21	4xM5x20	4,2	61	41	23	✔	31,44 €
RT61-24-47/SS	24	47	32,0	26	4xM6x24	7,3	96	44	23	✔	36,62 €
RT61-25-47/SS	25	47	32,0	26	4xM6x24	7,3	100	43	23	✔	39,49 €

*Depending on availability - Dimensions in mm

Self-centering locking assembly Ste ★★★

RT70 Medium/high torque

- **Inserts between the shaft and the bore**
- High transmissible torque
- Contact pressure spread evenly
- Easy to assemble and dismantle
- Backlash free
- No constraints due to keyway
- **Increases the resistant part of the section of the shaft**
- Suitable for alternating rotational movements
- Materials:
  Body: steel
  Screws: steel DIN 912 12.9






NUOVO !

Options


- Other diameters available (up to 180mm bore)

Info.

- * PN: hub surface pressure
- * PW: shaft surface pressure







DISCOUNTS

Qty	1+	6+	20+	40+	60+	100+
Disc.	List	-10%	-15%	-20%	-25%	On request

Part number	ØA	ØD	L1	L2	L3	L	Transmissible torque (Nm)	Pw (N/mm²)	PN (N/mm²)	No.	Screws Type	Tightening torque (Nm)	Stock*	Price each 1 to 5
RT70-19-47	19	47	26	31	39	45	350	228	98	4	M6x25	17	✔	13,69 €
RT70-20-47	20	47	26	31	39	45	390	231	100	4	M6x25	17	✔	13,69 €
RT70-22-47	22	47	26	31	39	45	440	220	95	4	M6x25	17	✔	13,69 €
RT70-24-50	24	50	26	31	39	45	519	215	102	6	M6x25	17	-	14,86 €
RT70-25-50	25	50	26	31	39	45	590	230	105	6	M6x25	17	✔	14,94 €
RT70-28-55	28	55	26	31	39	45	700	220	110	6	M6x25	17	✔	16,91 €
RT70-30-55	30	55	26	31	39	45	760	200	120	6	M6x25	17	✔	16,47 €
RT70-32-60	32	60	26	31	39	45	930	230	114	8	M6x25	17	✔	18,37 €
RT70-35-60	35	60	26	31	39	45	1030	200	119	8	M6x25	17	✔	18,50 €
RT70-38-65	38	65	26	31	39	45	1240	210	124	8	M6x25	17	-	20,85 €
RT70-40-65	40	65	26	31	39	45	1350	200	125	8	M6x25	17	✔	20,88 €
RT70-42-75	42	75	30	36	47	55	2170	236	140	6	M8x30	41	-	26,96 €
RT70-45-75	45	75	30	36	47	55	2350	236	140	6	M8x30	41	-	27,10 €
RT70-48-80	48	80	30	36	47	55	2510	218	135	6	M8x30	41	-	30,14 €
RT70-50-80	50	80	30	36	47	55	2580	218	135	6	M8x30	41	✔	30,25 €
RT70-55-85	55	85	30	36	47	55	3200	223	145	8	M8x30	41	-	34,35 €
RT70-60-90	60	90	30	36	47	55	3380	198	157	8	M8x30	41	✔	36,79 €
RT70-65-95	65	95	30	36	47	55	4160	213	140	8	M8x30	41	-	37,62 €
RT70-70-110	70	110	40	46	57	67	6840	225	143	8	M10x35	83	-	56,95 €


*Depending of availability - Dimensions in mm

Self-centering locking assembly

High torque

RTL450

- ***Inserts between the shaft and the bore***
- *High transmissible torque*
- *Contact pressure spread evenly*
- *Easy to assembly and dismantle*
- *Reduced width*
- *Backlash free*
- *No constraints due to keyway*
- ***Increases the resistant part of the section of the shaft***
- *Suitable for alternating rotational movements*
- *Up to 3 units can be used together*
- *Material:*
  Steel






NUOVO !

Options

- *Other diameters available (up to 300mm bore)*

Info.

- **PN: hub surface pressure*
- **PW: shaft surface pressure*



DISCOUNTS

Qty	1+	6+	20+	40+	60+	100+
Disc.	List	-10%	-15%	-20%	-25%	On request

Part number	ØA	ØD	B	L	C	Screw M	Tightening torque TA (Nm)	Transmissible torque T (Nm)	*Pw (N/mm²)	*PN (N/mm²)	Stock*	Price each 1 to 5
RTL450-25-55	25	55	32	40	46	6xM6x35	17	295	295	134	✔	28,72 €
RTL450-30-55	30	55	32	40	46	6xM6x35	17	246	246	134	✔	29,65 €
RTL450-35-60	35	60	44	54	60	7xM6x45	17	174	174	101	✔	35,99 €
RTL450-38-75	38	75	44	54	62	7xM8x50	41	296	296	150	-	44,60 €
RTL450-40-75	40	75	44	54	62	7xM8x50	41	281	281	150	✔	45,79 €
RTL450-42-75	42	75	44	54	62	7xM8x50	41	268	268	150	-	48,20 €
RTL450-45-75	45	75	44	54	62	7xM8x50	41	250	250	150	-	48,38 €
RTL450-48-80	48	80	44	54	62	8xM8x50	41	207	207	124	-	55,55 €
RTL450-50-80	50	80	56	64	72	8xM8x50	41	200	200	98	✔	55,60 €
RTL450-55-85	55	85	56	64	72	9xM8x50	41	205	205	104	✔	62,96 €
RTL450-60-90	60	90	56	64	72	10xM8x50	41	202	202	106	✔	67,78 €
RTL450-65-95	65	95	56	64	72	10xM8x50	41	187	187	100	-	72,83 €
RTL450-70-110	70	110	70	78	88	10xM10x60	83	223	223	114	-	98,29 €
RTL450-75-115	75	115	70	78	88	10xM10x60	83	223	223	114	✔	106,70 €
RTL450-80-120	80	120	70	78	88	11xM10x60	83	215	215	115	-	113,46 €
RTL450-85-125	85	125	70	78	88	12xM10x60	83	215	215	115	-	122,09 €
RTL450-90-130	90	130	70	78	88	12xM10x60	83	208	208	115	-	125,75 €
RTL450-95-135	95	135	70	78	88	12xM10x60	83	208	208	115	-	142,37 €
RTL450-100-145	100	145	90	100	112	11xM12x80	145	200	200	107	-	188,49 €

**Depending of availability - Dimensions in mm*