


- Modulo da 1 a 2,5
- Angolo di pressione 20°
- Dentatura Gleason
- Precisione JIS B 1704: 1978 grado 3
- Materiale:  
Inox 303
- Durezza dentatura < 187HB
- Per una coppia occorrono due componenti

**NUOVO!****SCONTI PER QUANTITÀ**

Qtà	1+	6+	10+
Sc.	Prix -12%	Su richiesta	

Codice	Modulo	Denti		ØA								Massa (g)	Prezzo unit. da 1 a 5		
		Z	H7	ØB	ØC	ØD	E	F	G	H	N			J	K
SSB1-20-RA	1	20	6	16	20	21,41	20	13,95	10,71	8	12	5	9,86	0,019	69,48 €
SSB1-25-RA		25	6	20	25	26,41	23	15,16	11,21	8	14	6	15,03	0,035	76,59 €
SSB1-30-RA		30	8	24	30	31,41	28	17,71	13,71	10	16	6	19,03	0,057	Su richiesta
SSB1.5-20-RA	1,5	20	8	26	30	32,12	30	21,24	16,06	13	19	8	15,37	0,074	88,34 €
SSB1.5-25-RA		25	10	30	37,5	39,62	34	22,25	16,31	11,5	19	9	19,54	0,11	110,47 €
SSB1.5-30-RA		30	10	36	45	47,12	43	28,24	21,56	16	25	10	25,72	0,21	Su richiesta
SSB2-20-RA	2	20	12	34	40	42,83	37	24,89	18,41	14	22	10	21,72	0,15	128,75 €
SSB2-25-RA		25	12	45	50	52,83	40	24,33	16,41	12,5	20	12	26,06	0,24	160,33 €
SSB2-30-RA		30	12	45	60	62,83	50	29,43	21,41	12,5	25	12	36,06	0,37	240,37 €
SSB2.5-20-RA	2,5	20	14	42	50	53,54	48	32,54	24,77	19	29	12	28,06	0,30	182,87 €
SSB2.5-25-RA		25	16	55	62,5	66,04	50	30,41	20,52	15	26	15	34,57	0,46	236,98 €
SSB2.5-30-RA		30	16	60	75	78,54	62	36,28	26,27	17	32	15	47,57	0,76	368,54 €

Dimensioni in mm

## Rapporto

# 1,5:1 2:1 3:1

## Inox 303

- Modulo da 1 a 2,5
- Angolo di pressione 20°
- Dentatura Gleason
- Precisione JIS B 1704: 1978 grado 3
- Materiale: Inox 303
- Durezza dentatura < 187HB
- Per una coppia occorrono due componenti




**NUOVO!**

### SCONTI PER QUANTITÀ

Qtà	1+	6+	10+
Sc.	Prix	-12%	Su richiesta

Codice	Modulo	Denti ØA		ØB	ØC	ØD	E	F	G	H	N	J	K	Massa (g)	Prezzo unit. da 1 a 5
		Z	H7												
<b>Rapporto 1,5:1</b>															
SSHB1.5-20-RA	1,5	20	8	25	30	33,13	33	18,63	11,54	8,83	17	9	17,05	0,063	95,57 €
SSHB1.5-30-RA		30	10	30	45	46,24	28	18,53	13,93	8	16	9	27,37	0,120	147,19 €
SSHB2-20-RA	2	20	10	35	40	44,18	45	25,06	16,39	13,33	22	11	21,34	0,160	142,70 €
SSHB2-30-RA		30	10	35	60	61,65	40	26,87	21,24	15	23	11	37,56	0,260	224,76 €
SSHB2.5-20-RA	2,5	20	12	40	50	55,22	55	31,06	19,24	14,16	28	15	27,42	0,280	204,71 €
SSHB2.5-30-RA		30	15	45	75	77,07	50	34,22	26,55	18	30	15	45,61	0,540	347,99 €
<b>Rapporto 2:1</b>															
SSDB1.5-20-RA	1,5	20	8	25	30	33,61	46	25,54	16,9	14,75	24	10	17,28	0,088	102,03 €
SSDB1.5-40-RA		40	10	38	60	60,88	35	25,01	20,88	15	22	10	39,64	0,270	228,96 €
SSDB2-20-RA	2	20	12	32	40	44,81	60	34,16	21,2	18	32	15	20,92	0,190	160,70 €
SSDB2-40-RA		40	12	50	80	81,17	45	32,37	26,17	18	27	15	48,46	0,610	372,68 €
SSDB2.5-20-RA	2,5	20	12	40	50	56,01	75	43,78	26,5	22,5	41	20	24,56	0,400	249,74 €
SSDB2.5-40-RA		40	15	60	100	101,46	55	39,73	31,46	20	35	20	60,28	1,210	629,33 €

Dimensioni in mm



## SCONTI PER QUANTITÀ

Qtà	1+	6+	10+
Sc.	Prix	-12%	Su richiesta

Codice	Modulo	Denti Z	ØA H7	ØB	ØC	ØD	E	F	G	H	N	J	K	Massa (g)	Prezzo unit. da 1 a 5
<b>Rapporto 3:1</b>															
SSTB1.5-15-RA	1.5	15	8	18	22,5	26,54	47	23,19	13,92	12,5	22,5	10	14,75	0,041	76,21 €
SSTB1.5-45-RA		45	10	36	67,5	68,06	28	20,44	17,59	11	17	10	46,58	0,250	249,00 €
SSTB2-15-RA	2	15	10	24	30	35,35	60	29,8	15,89	14	29	15	19,13	0,095	110,45 €
SSTB2-45-RA		45	12	60	90	90,75	40	30,4	26,12	17	26	15	59,04	0,800	435,38 €
SSTB2.5-15-RA	2.5	15	12	30	37,5	44,18	75	38,41	19,86	17,5	37	20	20,51	0,190	156,56 €
SSTB2.5-45-RA		45	15	60	112,5	113,43	50	38,35	32,65	22	35	20	72,84	1,360	725,26 €

Dimensioni in mm