

T type tooth bar stock



T10-BAR

Aluminium





- Bar stock to be cut to length by the customer

- The overall length is the same as the maximum length

- Material : Aluminium suitable for hard anodic oxidation

- Finish : Supplied not-treated



Info.

- We are unable to modify this product



DISCOUNTS

Qty	1+	6+	20+	40+
disc.	List -12%	List -25%	On request	

Part number	Z Teeth	ØD External	Length of teeth L _D	Total length L _T	Price each 1 to 5
10T10-BAR	10	29,98	140	140	12,81 €
11T10-BAR	11	33,16	140	140	14,99 €
12T10-BAR	12	36,35	140	140	17,42 €
13T10-BAR	13	39,55	140	140	18,77 €
14T10-BAR	14	42,70	140	140	23,63 €
15T10-BAR	15	45,90	140	140	26,20 €
16T10-BAR	16	49,10	160	160	29,80 €
17T10-BAR	17	52,25	160	160	32,70 €
18T10-BAR	18	55,45	160	160	35,80 €
19T10-BAR	19	58,65	160	160	40,08 €
20T10-BAR	20	61,80	160	160	43,55 €
21T10-BAR	21	65,00	160	160	47,29 €
22T10-BAR	22	68,15	160	160	55,90 €
23T10-BAR	23	71,35	160	160	56,40 €
24T10-BAR	24	74,55	160	160	62,97 €
26T10-BAR	26	80,90	160	160	70,64 €
28T10-BAR	28	87,25	160	160	78,64 €
30T10-BAR	30	93,65	160	160	95,34 €
32T10-BAR	32	100,00	160	160	104,67 €
34T10-BAR	34	106,40	160	160	114,45 €
36T10-BAR	36	112,75	160	160	127,23 €
38T10-BAR	38	119,10	160	160	145,75 €
40T10-BAR	40	125,45	160	160	157,29 €
45T10-BAR	45	141,40	160	160	207,80 €
48T10-BAR	48	150,95	160	160	222,12 €
60T10-BAR	60	189,15	160	160	365,92 €
72T10-BAR	72	227,29	160	160	523,43 €

Dimensioni in mm