

# T type tooth bar stock




## T2.5-BAR

## Aluminium




**-30%**

- Bar stock to be cut to length by the customer
- The overall length is the same as the maximum length
- Material : Aluminium suitable for hard anodic oxidation
- Finish : Supplied not-treated



### Info.

- We are unable to modify this product



### DISCOUNTS

Qty	1+	6+	20+	40+
disc.	List -12%	-25%	On request	

Part number	Z Teeth	ØD External	Length of teeth L <sub>b</sub>	Total length L <sub>T</sub>	Price each 1 to 5
10T2.5-BAR	10	7,45	50	75	2,35 €
12T2.5-BAR	12	9,00	50	75	2,42 €
13T2.5-BAR	13	9,80	50	75	2,52 €
14T2.5-BAR	14	10,60	50	75	2,67 €
15T2.5-BAR	15	11,40	50	75	2,85 €
16T2.5-BAR	16	12,20	50	75	2,92 €
17T2.5-BAR	17	13,00	50	75	2,99 €
18T2.5-BAR	18	13,80	50	75	3,10 €
19T2.5-BAR	19	14,60	90	120	5,64 €
20T2.5-BAR	20	15,40	90	120	5,88 €
21T2.5-BAR	21	16,20	90	120	6,42 €
22T2.5-BAR	22	17,00	125	140	8,35 €
24T2.5-BAR	24	18,55	125	140	9,06 €
26T2.5-BAR	26	20,15	125	140	9,92 €
27T2.5-BAR	27	20,95	125	140	10,02 €
28T2.5-BAR	28	21,75	125	140	10,28 €
29T2.5-BAR	29	22,55	125	140	10,88 €
30T2.5-BAR	30	23,35	125	140	10,95 €
32T2.5-BAR	32	24,95	125	140	11,85 €
34T2.5-BAR	34	26,55	125	140	12,45 €
35T2.5-BAR	35	27,35	132	140	13,23 €
36T2.5-BAR	36	28,10	132	140	14,20 €
38T2.5-BAR	38	29,70	140	140	14,45 €
40T2.5-BAR	40	31,30	140	140	15,59 €
42T2.5-BAR	42	32,90	140	140	17,35 €
44T2.5-BAR	44	34,50	140	140	19,27 €
45T2.5-BAR	45	35,30	140	140	19,66 €
48T2.5-BAR	48	37,70	140	140	20,80 €
50T2.5-BAR	50	39,29	160	160	25,27 €
60T2.5-BAR	60	47,25	160	160	32,77 €
65T2.5-BAR	65	51,20	160	160	37,87 €
70T2.5-BAR	70	55,20	160	160	41,44 €
72T2.5-BAR	72	56,80	160	160	43,72 €
90T2.5-BAR	90	71,12	160	160	63,43 €
100T2.5-BAR	100	79,08	160	160	84,82 €

Dimensions in mm