

-30%




- Bar stock to be cut to length by the customer
- The overall length is the same as the maximum length
- Material : Aluminium suitable for hard anodic oxidation
- Finish : Supplied not-treated



Info.

- We are unable to modify this product



DISCOUNTS

Qty	1+	6+	20+	40+
disc.	List -12%	-25%	On request	

Part number	Z Teeth	ØD External	Length of teeth L _b	Total length L _r	Price each 1 to 5
10T5-BAR	10	15,05	125	140	6,81 €
11T5-BAR	11	16,65	125	140	7,38 €
12T5-BAR	12	18,25	125	140	8,06 €
13T5-BAR	13	19,85	125	140	8,09 €
14T5-BAR	14	21,45	140	140	9,45 €
15T5-BAR	15	23,05	140	140	10,24 €
16T5-BAR	16	24,60	140	140	11,49 €
17T5-BAR	17	26,20	140	140	12,02 €
18T5-BAR	18	27,00	140	140	13,35 €
19T5-BAR	19	29,40	140	140	14,49 €
20T5-BAR	20	31,00	160	160	16,66 €
21T5-BAR	21	32,70	160	160	17,38 €
22T5-BAR	22	34,15	160	160	19,34 €
23T5-BAR	23	35,85	160	160	19,52 €
24T5-BAR	24	37,40	160	160	20,95 €
25T5-BAR	25	38,95	160	160	22,49 €
26T5-BAR	26	40,60	160	160	24,80 €
27T5-BAR	27	42,20	160	160	24,99 €
28T5-BAR	28	43,75	160	160	27,51 €
29T5-BAR	29	45,35	160	160	27,63 €
30T5-BAR	30	46,95	160	160	29,44 €
32T5-BAR	32	50,10	160	160	34,20 €
34T5-BAR	34	53,25	160	160	37,37 €
35T5-BAR	35	54,85	160	160	37,62 €
36T5-BAR	36	56,45	160	160	39,72 €
37T5-BAR	37	58,06	160	160	41,94 €
38T5-BAR	38	59,65	160	160	42,15 €
40T5-BAR	40	62,85	160	160	45,83 €
42T5-BAR	42	66,00	160	160	49,72 €
44T5-BAR	44	69,20	160	160	58,22 €
45T5-BAR	45	70,80	160	160	58,61 €
46T5-BAR	46	72,40	160	160	59,14 €
48T5-BAR	48	75,55	160	160	65,47 €
50T5-BAR	50	78,75	160	160	73,00 €
60T5-BAR	60	94,65	160	160	98,49 €
72T5-BAR	72	113,75	160	160	138,44 €
80T5-BAR	80	126,48	160	160	161,53 €
90T5-BAR	90	142,40	160	160	212,62 €
100T5-BAR	100	158,31	160	160	274,81 €