
Economic Mini-table with trapezoidal leadscrew


TBE10 — Max carried payload 1kg

- ***Leadscrew table for manual use***
- Right hand trapezoidal leascrew TR10x2
- Guided by 2 shaft in steel on 4 brass bearings
- Axial accuracy < 0,20mm
- With clamping wingnut and grip knob
- Materials:
  Anodised aluminium and steel
- Working T° : from +5°C to +80°C





Accessories

- Base plate with ruler
  TBE-BASE (vol. 1 p.619)



Admissible payload





	Static	Dynamic
Fmax (daN)	10	2,5
Cmax (Nm)	4	1
Mmax (Nm)	5	1

(40mm<r<100mm)

DISCOUNTS

Qty	1+	2+	3+
Disc.	List	-10%	On request


Part number	Stroke (mm)	Max carried payload (kg)	Weight (kg)	Price each
TBE10-50	50	1	0,51	246,19 €
TBE10-100	100	1	0,59	248,63 €

Dimensions in mm

Economic Mini-table with trapezoidal leadscrew


Max carried payload 2kg — TBE12

- ***Leadscrew table for manual use***
- Right hand trapezoidal leascrew TR10x2
- Guided by 2 shaft in steel on 4 brass bearings
- Axial accuracy < 0,20mm
- With clamping wingnut and grip knob
- Materials:
  Anodised aluminium and steel
- Working T° : from +5°C to +80°C





Accessories

- Base plate with ruler
  TBE-BASE (vol. 1 p.619)



Admissible payload





	Static	Dynamic
Fmax (daN)	20	5
Cmax (Nm)	8	2
Mmax (Nm)	10	2

(50mm<r<150mm)

DISCOUNTS

Qty	1+	2+	3+
Disc.	List	-10%	On request


Part number	Stroke (mm)	Max carried payload (kg)	Weight (kg)	Price each
TBE12-50	50	2	0,91	278,30 €
TBE12-100	100	2	1,02	281,34 €
TBE12-150	150	2	1,13	284,37 €
TBE12-200	200	2	1,24	287,41 €

Dimensions in mm

Economic Mini-table with trapezoidal leadscrew


TBE16 — Max carried payload 5kg

- ***Leadscrew table for manual use***
- *Right hand trapezoidal leascrew TR12x3*
- *Guided by 2 shaft in steel on 4 brass bearings*
- *Axial accuracy < 0,20mm*
- *With clamping wingnut and grip knob*
- *Materials:*
  Anodised aluminium and steel
- *Working T° : from +5°C to +80°C*





Accessories

- *Base plate with ruler*
  TBE-BASE (vol. 1 p.619)



Admissible payload





	Static	Dynamic
Fmax (daN)	40	12
Cmax (Nm)	17	4
Mmax (Nm)	20	5

(60mm<r<200mm)

DISCOUNTS

Qty	1+	2+	3+
Disc.	List	-10%	On request

Part number	Stroke (mm)	Max carried payload (kg)	Weight (kg)	Price each
TBE16-50	50	5	1,53	306,18 €
TBE16-100	100	5	1,71	309,81 €
TBE16-150	150	5	1,89	313,45 €
TBE16-200	200	5	2,07	317,08 €

Dimensions in mm


Base plate for economic mini-table


Allows X-Y cross tables

TBE BASE


- ***Base plate with ruler***
- *To be screwed under the end supports*
- *Allows mounting in XY cross tables thanks to counterbored holes*
- *Ruler with graduation in mm*
- *Delivered with 8 fixing screws*
- *Material:*
  Plate Anodised aluminium
  Stainless steel ruler
  Zinc plated fixing screws

NUOVO !






Simple assembly



Cross tables assembly



DISCOUNTS

Qty	1+	2+	3+
Disc.	List	-10%	On request

Part number	For table	Stroke (mm)	C	HB	LB	E0	E1	F	ØD1	ØD2	P2	Weight (kg)	Price each
TBE10-50/BASE	TBE10	50	69	9,0	110	26	59	12	5,2	9	5,0	0,20	56,03 €
TBE10-100/BASE	TBE10	100	69	9,0	160	26	59	12	5,2	9	5,0	0,28	63,55 €
TBE12-50/BASE	TBE12	50	83	9,5	132	46	73	12	6,5	11	6,5	0,30	76,19 €
TBE12-100/BASE	TBE12	100	83	9,5	182	46	73	12	6,5	11	6,5	0,40	82,26 €
TBE12-150/BASE	TBE12	150	83	9,5	232	46	73	12	6,5	11	6,5	0,50	88,56 €
TBE12-200/BASE	TBE12	200	83	9,5	282	46	73	12	6,5	11	6,5	0,60	94,78 €
TBE16-50/BASE	TBE16	50	98	11,5	150	58	88	16	6,5	11	6,5	0,47	83,96 €
TBE16-100/BASE	TBE16	100	98	11,5	200	58	88	16	6,5	11	6,5	0,62	92,62 €
TBE16-150/BASE	TBE16	150	98	11,5	250	58	88	16	6,5	11	6,5	0,77	101,15 €
TBE16-200/BASE	TBE16	200	98	11,5	300	58	88	16	6,5	11	6,5	0,92	109,64 €

Dimensions in mm