Automatic chain tensioner

With sprocket


TCRX

- ***Tensioner for single chain***
- *Materials:*
  Housing and column: polyamide reinforced with 30% glass fibre
  Screws and springs: stainless steel 304L
  Steel version: bracket and sprocket steel
  Stainless steel version: bracket, axle and nut stainless steel 304L, stainless steel sprocket, sprocket bearing lubricated for life (FM 222 grease suitable for food industry acc USA standards.



Accessories

- *For use with* ***SBR*** *or* ***SBS*** *chains*
  (tome 2 *p.222-224*)



IN STOCK*
Otherwise contact us

DISCOUNTS

Qty	1+	4+	10+
Disc.	List	-10%	On request

Part number	Chain	Pitch	N° of teeth	S	Øext	ØPCD	F	E	H	Stroke	Tension (N)	Price each 1 to 3
Steel sprocket												
TCRX-06B1	06B1	9,525	15	5,3	49,3	45,81	160	135,0	95,0	40	100 to 240	69,44 €
TCRX-08B1	08B1	12,700	15	7,2	65,5	61,09	186	153,5	113,5	40	100 to 240	68,74 €
TCRX-10B1	10B1	15,875	15	9,1	83,0	76,36	196	153,5	113,5	40	100 to 240	73,42 €
Stainless steel sprocket												
TCRX-06B1/SS	06B1	9,525	15	5,3	49,3	45,81	160	135,0	95,0	40	100 to 240	85,72 €
TCRX-08B1/SS	08B1	12,700	15	7,2	65,5	61,09	186	153,5	113,5	40	100 to 240	91,18 €
TCRX-10B1/SS	10B1	15,875	15	9,1	83,0	76,36	196	153,5	113,5	40	100 to 240	116,48 €

**Depending on availability - Dimensions in mm*

Automatic chain tensioner

TCLAR

With wide guide

- ***Tensioner for single chain***
- *Materials:*
  Housing: polyamide reinforced with 30% glass fibre
  Profile: Green HD1000 polyethylene
  Machined column: Black HD500 polyethylene
  Screws and springs: stainless steel 304L




NUOVO !


Adjustment

- *Tension pressure can be reduced by loosening the springs, see instructions*

Accessories

- *To use with* ***SBR*** *or* ***SBS*** *chains* **(tome 2 p.222-224)**





DISCOUNTS

Qty	1+	4+	10+
Disc.	List	-10%	On request

Part number	Chain	A	C	Stroke	Tension (N) 1 spring	2 springs	3 springs	Price each 1 to 3
TCL-AR-06B1	06B1	5	30	40	60 to 132	120 to 264	180 to 396	127,52 €
TCL-AR-08B1	08B1	7	30	40	60 to 132	120 to 264	180 to 396	127,52 €
TCL-AR-10B1	10B1	9	30	40	60 to 132	120 to 264	180 to 396	127,52 €
TCL-AR-12B1	12B1	11	30	40	60 to 132	120 to 264	180 to 396	127,52 €

Dimensions in mm

Automatic chain tensioner

With guide

TCSH


- ***Tensioner for single chain***
- *Materials:*
  Housing and column: polyamide reinforced with 30% glass fibre
  Profile: Green HD1000 polyethylene
  Screws and springs: stainless steel 304L

Accessories

- *For use with **SBR** or **SBS** chains*
  (tome 2 p.222-224)



NUOVO !



DISCOUNTS

Qty	1+	4+	10+
Disc.	List	-10%	On request

Part number	Chain	A	C	Stroke	Tension (N)	Stock*	Price each 1 to 3
TCSH-06B1	06B1	5	20	40	100 to 240	✔	40,98 €
TCSH-08B1	08B1	7	20	40	100 to 240	✔	40,98 €
TCSH-10B1	10B1	9	20	40	100 to 240	✔	40,98 €
TCSH-12B1	12B1	11	20	40	100 to 240	✔	40,98 €

**Depending on availability - Dimensions in mm*