
Hexagonal headed bolt with narrow shaft

VHTM HDSS

Hygienic Design®




- ***Thin shaft bolts for use in hygienic environments***
- *Material:*
  Stainless steel 1.4404 (316L)
  Polished finish Ra<0.8

Advantages

- *In combination with a clamping element, these thin shafted screws are designed against becoming detached accidentally, thus meeting the requirements of European standard 2006/42/EG*
- *Dirt and residues of product or cleaning materials will not remain, ensuring easy cleaning*

Accessories

- **RDS** *safety washer to secure the screw to the other component before assembly* *(see page 60)*



DISCOUNTS

Qty	1+	5+	10+	25+	50+
Disc.	Net	-5%	-10%	-15%	On request

Part number	ØD	ØD1	ØD2	H	B	K	L	SW	Price each 1 to 4
VHTM4-8/HDSS	M4	9,2	3,1	3,0	5,0	4,0	8	7	7,17 €
VHTM4-10/HDSS	M4	9,2	3,1	3,0	5,0	4,0	10	7	7,20 €
VHTM4-12/HDSS	M4	9,2	3,1	3,0	5,0	4,0	12	7	7,30 €
VHTM4-16/HDSS	M4	9,2	3,1	3,0	5,0	4,0	16	7	7,37 €
VHTM4-20/HDSS	M4	9,2	3,1	3,0	14,0	4,0	20	7	7,44 €
VHTM5-10/HDSS	M5	10,5	3,7	3,7	6,0	4,7	10	8	7,53 €
VHTM5-12/HDSS	M5	10,5	3,7	3,7	6,0	4,7	12	8	7,64 €
VHTM5-16/HDSS	M5	10,5	3,7	3,7	6,0	4,7	16	8	7,73 €
VHTM5-20/HDSS	M5	10,5	3,7	3,7	6,0	4,7	20	8	7,79 €
VHTM5-25/HDSS	M5	10,5	3,7	3,7	16,0	4,7	25	8	7,92 €

All dimensions in mm

Part number	ØD	ØD1	ØD2	H	B	K	L	SW	Price each 1 to 4
VHTM6-12/HDSS	M6	13,0	4,2	4,0	7,0	5,0	12	10	8,26 €
VHTM6-16/HDSS	M6	13,0	4,2	4,0	7,0	5,0	16	10	8,42 €
VHTM6-20/HDSS	M6	13,0	4,2	4,0	7,0	5,0	20	10	8,55 €
VHTM6-25/HDSS	M6	13,0	4,2	4,0	18,0	5,0	25	10	8,83 €
VHTM6-30/HDSS	M6	13,0	4,2	4,0	18,0	5,0	30	10	8,98 €
VHTM6-35/HDSS	M6	13,0	4,2	4,0	18,0	5,0	35	10	9,14 €
VHTM6-40/HDSS	M6	13,0	4,2	4,0	18,0	5,0	40	10	9,41 €
VHTM6-45/HDSS	M6	13,0	4,2	4,0	18,0	5,0	45	10	9,60 €
VHTM6-50/HDSS	M6	13,0	4,2	4,0	18,0	5,0	50	10	9,77 €
VHTM6-60/HDSS	M6	13,0	4,2	4,0	18,0	5,0	60	10	10,22 €
VHTM8-16/HDSS	M8	16,8	6,0	5,5	9,5	6,5	16	13	9,30 €
VHTM8-20/HDSS	M8	16,8	6,0	5,5	9,5	6,5	20	13	9,60 €
VHTM8-25/HDSS	M8	16,8	6,0	5,5	9,5	6,5	25	13	9,84 €
VHTM8-30/HDSS	M8	16,8	6,0	5,5	22,0	6,5	30	13	10,19 €
VHTM8-35/HDSS	M8	16,8	6,0	5,5	22,0	6,5	35	13	10,46 €
VHTM8-40/HDSS	M8	16,8	6,0	5,5	22,0	6,5	40	13	10,74 €
VHTM8-45/HDSS	M8	16,8	6,0	5,5	22,0	6,5	45	13	11,06 €
VHTM8-50/HDSS	M8	16,8	6,0	5,5	22,0	6,5	50	13	11,34 €
VHTM8-60/HDSS	M8	16,8	6,0	5,5	22,0	6,5	60	13	11,93 €
VHTM8-65/HDSS	M8	16,8	6,0	5,5	22,0	6,5	65	13	10,91 €
VHTM8-70/HDSS	M8	16,8	6,0	5,5	22,0	6,5	70	13	12,58 €
VHTM10-20/HDSS	M10	20,6	7,7	7,3	12,0	8,3	20	16	11,06 €
VHTM10-25/HDSS	M10	20,6	7,7	7,3	12,0	8,3	25	16	11,47 €
VHTM10-30/HDSS	M10	20,6	7,7	7,3	12,0	8,3	30	16	11,93 €
VHTM10-35/HDSS	M10	20,6	7,7	7,3	12,0	8,3	35	16	12,34 €
VHTM10-40/HDSS	M10	20,6	7,7	7,3	26,0	8,3	40	16	12,83 €
VHTM10-45/HDSS	M10	20,6	7,7	7,3	26,0	8,3	45	16	13,28 €
VHTM10-50/HDSS	M10	20,6	7,7	7,3	26,0	8,3	50	16	13,75 €
VHTM10-60/HDSS	M10	20,6	7,7	7,3	26,0	8,3	60	16	14,67 €
VHTM10-70/HDSS	M10	20,6	7,7	7,3	26,0	8,3	70	16	15,69 €
VHTM10-80/HDSS	M10	20,6	7,7	7,3	26,0	8,3	80	16	16,70 €

All dimensions in mm