Thermoplastic

VTLB

- ***Operating element***
- *Insert with tapped through hole*
- *Working T° range -30°C to +130°C*
- *Materials*
  Black polyamide PA6 glass fiber reinforced
  Brass or stainless steel 303 insert

Strong tightening





NUOVO !

Big diameter

Advantages

Handwheel size up to 100mm diameter provides excellent grip and clamping force





DISCOUNTS

Qty	1+	10+	20+	50+	100+
Disc.	List	-5%	-10%	-15%	On request

Part number Brass insert	Stainless steel insert	ØA	ØB	C	ØD	E	H	ØD1	ØK	Weight (g)	Price each 1 to 9 Brass	Stainless steel
VTLB8-63	VTLB8-63/SS	63	21	21	M8	18,5	30	12,5	Ø15	30	7,48 €	13,34 €
VTLB10-63	-	63	21	21	M10	18,5	30	12,5	Ø15	34	7,74 €	-
VTLB10-80	VTLB10-80/SS	80	26	23	M10	25	35	13	Ø20	59	9,11 €	13,62 €
VTLB12-80	-	80	26	23	M12	25	35	13	Ø20	61	9,88 €	-
VTLB12-100	VTLB12-100/SS	100	30	25	M12	25	38	17	Ø25	87	12,82 €	18,54 €
VTLB14-100	-	100	30	25	M14	25	38	17	Ø25	89	13,88 €	-

Dimensions in mm