
Connection plate for aluminium profile

ACLPL — For pre-assembled connection


- ***For connecting two structures together***
- *Connection of 2 aluminium profiles*
- *Corner reinforcement*
- *Material:*
  Anodised aluminium

Info.

- *Supplied without fixing kit (see button head screw* ***BHC8-16/SS/B*** *or* ***BHC8-20/SS*** *and slot nut* ***PRF-ECL-M8/SS)***




Anodised aluminium






Typical application


Aluminium profile





ACL-PL-9090





ACL-PL-90180

DISCOUNTS

Qty	1+	50+	100+
Disc.	Net	-5%	On request

Part N°	L	B	H	A	ØD	Weight (g)	Price each 1 to 49
Square							
ACL-PL-9090	86	-	6	45	9	115	6,63 €
Rectangular							
ACL-PL-90180	176	86	6	45	9	240	11,30 €

All dimensions in mm

0 825 88 5000
Service 0,15 € / min
+ prix appel

Altri prodotti...



Piede fissabile con snodo - poliammide, Ø 50



Maniglia a ponte, Fino a 250°C



Tenditore rigido, Manuale



Sfera portante, Forte



Clip di fissaggio per cavi per profili alluminio, Per canalina di ca...



Volantino a 6 lobi, Duroplast - Inox



Attrezzo di bloccaggio a tirante, A tirante - acciaio



Ingran. dritto di precisione trattato skiving, Acciaio 20NCD2 cement...



Riduttore a ruota e vite senza fine, fino a 980 Nm



Spina cilindrica, standard DIN 6325



Giunto di collegamento, Ad angolo fisso




Tavola di posizionamento verticale manuale, 7kg

Prodotti correlati



Vite a testa bombata BHC , Inox A2



Fissaggio, Dado quadrato con linguetta - Inox



Elementi di giunzione, Piastra di fissaggio - 86x86 mm



Elementi di giunzione, Collegamento angolare