# Connection plate for aluminium profile


## Angle connection

## ACLPL


- ***Connection of 2 aluminium profiles***
- *Corner reinforcement*
- *Material:*
  *Anodised aluminium*


**Info.**

- *Supplied without fixing kit (see button head screw* **BHC8-16/SS/B** *or* **BHC8-20/SS** *and slot nut* **PRF-ECL-M8/SS**)




Anodised aluminium






**Typical application**




**ACL-PL-135**




**ACL-PL-180**

## DISCOUNTS

| Qty | 1+ | 50+ | 100+ |
|---|---|---|---|
| Disc. | Net | -5% | On request |

| Part N° | L | H | A | K | ØD | Weight (g) | Price each 1 to 49 |
|---|---|---|---|---|---|---|---|
| ACL-PL-135 | 131 | 6 | 45 | 41 | 9 | 210 | 14,57 € |
| ACL-PL-180 | 176 | 6 | 45 | 86 | 9 | 425 | 23,94 € |

*All dimensions in mm*

# Altri prodotti...




Ingranaggio elicoidale ad assi paralleli, Acciaio 20NCD2




Accessori di collegamento, Kit di fissaggio




Calettatore di bloccaggio autocentrante acciaio, Con ghiera




Cinghia aperta al metro tipo T, T10 Poliuretano armatura in acciaio




Braccio portaventosa orientabile, Serraggio standard




Ruote con supporto di livellamento, Ruote con supporto di livellamento




Pistoncino a molla, a leva




Dado cieco Hygienic Design®, Compatto




Cerniera invisibile, Invisibile - Apertura 90°




Rullo tendicinghia, Per ambienti aggressivi




Grano con punta a coppa, punta a coppa




Ingranaggio dritto acciaio - serie ECO, Acciaio C45

## Prodotti correlati




Vite a testa bombata BHC , Inox A2




Fissaggio, Dado quadrato con linguetta - Inox




Elementi di giunzione, Piastra di fissaggio - 86x86 mm




Elementi di giunzione, Piastra di fissaggio - 176x86 mm