Corner and variable angle hinge

ACLEAV
ACLPAV

- **Components for creating angled joints**
- Material
  Corner : Cast aluminium
  Hinge : chromed steel

Advantages


- Adjustable angle

Info

- No mounting screws supplied
  (see PRF-ECL-M8/screw FHC8 and CHC8)





ACL-EAV-45




ACL-PAV-130

NEW !





ACL-EAV-45



ACL-PAV-130

DISCOUNTS

Qty	1+	50+	100+
Disc.	List	-5%	On request

Part number	Type	Screw size	N	Weight (g)	Price each 1 to 49
ACL-EAV-45	Corner	M8	8/10	44	3,64 €
ACL-PAV-130	Hinge	M8	-	221	6,75 €

Dimensions in mm

Altri prodotti...


AC144

Piastrina di riscontro piatta per chiusura, 22mm


HG5-ECO

Ingranaggio dritto acciaio - serie ECO, Acciaio C45


SH2

Ingranaggio elicoidale ad assi paralleli, Plastica lavorata (delrin)


LPCM

Leva con impugnatura cilindrica, Duroplast nero, leva in acciaio


CHTRP

Riduttore a rinvio angolare a L o a T, fino a 87,3Nm


BABreglable

Perno autobloccante, Regolabile


UCP

Cuscinetto ritto in ghisa, Ghisa


T2

Cinghia di posizionamento T, T2.5 Poliuretano armatura in acciaio


E20


Riduttore a rinvio angolare, da 0.60 a 3.84 Nm


GARBAB

Perno di bloccaggio rapido manuale, A sfere


SH2

Ingranaggio elicoidale ad assi paralleli, Plastica lavorata


RBNpl

Ruota fissa con piastra, Acciaio - caucciù

Prodotti correlati


PRF4545

Profilato alluminio standard, 45 x 45 mm


PRF_ECL_

Fissaggio, Dado quadrato con linguetta - Acciaio