Adjustable foot for aluminium profile New

ACLALF

- **Mounting foot for aluminium structures that can be adjusted without tools**
- *Material:*
  Black fibreglass reinforced Nylon PA


Advantages


- *Easy to assemble in central tapped hole of* **PRF4545** *aluminium profile*
- *Supports up to 150 kg*


NEW!



Ideal for workstations







Assembly

DISCOUNTS

Qty	1+	50+	100+
Disc.	List	-5%	On request

Part number	B	H	N	ØM	B1	ØD	Max load (kg)	Weight (g)	Price each 1 to 49
ACL-ALF45-8-M8	45	45-65	8	M8	28	6,5	150	80	5,25 €

Dimensions in mm

Altri prodotti...


PRES

Accessori per pressa PRES-3HR e PRES-4HR, Portapinze


HDSS

Giunto cardanico - inox, Sollecitazioni intense


PLM-20SC

Magnete cilindrico di fermo filettato, Magnete di fermo maschiato


PFC

Piede fisso, Livellamento per piccoli elementi


CLASS

Maniglia a ripresa - maschio, Inox


SLHHlok

Bloccaggio a leva, A leva orizzontale / base orizzontale


PARF80


Piede senza snodo, Piede snodato oscillante fissabile Ø80


SH4

Ingranaggio elicoidale ad assi paralleli, Acciaio 20NCD2


ZBconique

Ingranaggio conico in plastica, 1:1


D19_D29

Molla di compressione al metro inox, al metro


SLHVlok

Bloccaggio a leva, A leva orrizontale / base verticale


HG5-ECO

Ingranaggio dritto acciaio - serie ECO, Acciaio C45

Prodotti correlati


PRF4545_P

Profilato alluminio per camera bianca, 45 x 45 mm