Right angled bracket for aluminium profiles

ACL EPP Connecting bracket for connecting 2 profiles

- **To join 2 profiles at 90°**
- Material
  Anodised aluminium
  For use with single slot profiles

Advantages

- Suitable for use with PRF aluminium profiles

Info

- No mounting screws supplied




ACL-EPP2-4545




ACL-EPP4-4590

NEW !









ACL-EPP2- 4545







ACL-EPP4-4590

DISCOUNTS

Qty	1+	50+	100+
Disc.	List	-5%	On request

Part number	Version	L	B	H	A	C	ØD	Weight (g)	Price each 1 to 49
ACL-EPP2-4545	2 holes	45	41	6	-	22,5	9	55	2,65 €
ACL-EPP4-4590	4 holes	90	41	6	45	22,5	9	112	5,27 €

Dimensions in mm

Right angled bracket for aluminium profiles

Connecting bracket for connecting 2 profiles ACL EPP

- **To join 2 profiles at 90°**
- Material
  Anodised aluminium
  For use with dual slot profilest

Advantages

- Suitable for use with PRF4590 aluminium profiles

Info

- No mounting screws supplied





ACL-EPP4-9045




ACL-EPP8-9090


NEW !





ACL-EPP4-9045





ACL-EPP8-9090

DISCOUNTS

Qty	1+	50+	100+
Disc.	List	-5%	On request

Part number	Version	L	B	H	A	C	ØD	Weight (g)	Price each 1 to 49
ACL-EPP4-9045	4 holes	45	86	6	45	22,5	9	112	5,45 €
ACL-EPP8-9090	8 holes	90	86	6	45	22,5	9	235	9,76 €

Dimensions in mm

Altri prodotti...



S2O

Supporto corto per manicotto aperto a sfere, Aperto - corto



RHTplss

Ruota alte temperature, fino a 200kg



CHAR5050_Z

Cerniera a molla, avvitabile



BGC

Giunto Oldham, con ganascia di serraggio



PRES2HR

Pressa manuale da banco, Pressione fino a 200kg



KS

Chiavetta in barre, Acciaio - in barre



ACL-PR

Elementi di giunzione, Collegamento a 90°



BLH70

Rinvio angolare a L, da 26 a 128 Nm



PT821

Pignone di trazione, Serie 821 e 805



NT92

Riduttore coassiale a treni paralleli, da 15 a 40 Nm - a treni



T5_11

Puleggia dentata di posizionamento tipo T, T5 alluminio



NCT

Giunto di collegamento, Ad angolo fisso

Prodotti correlati



PRF4545

Profilato alluminio standard, 45 x 45 mm