Roller block for aluminium profiles

Create your own roller track

ACLERP

- **Roller block for PRF aluminium profiles**
- Materials
  Black glass fibre reinforced nylon
  Rollers : POM
- Exists in 2 versions, with and without guide
- Max load : 100N each




ACL-ERP-SG





ACL-ERP-AG

Advantages


- Click to install








NEW !





DISCOUNTS

Qty	1+	50+	100+
Disc.	List	-5%	On request

Part number	Version	N	Weight (g)	Price each 1 to 49
ACL-ERP-SG	Without guide rail	8-10	43	3,82 €
ACL-ERP-AG	With guide rail	8-10	48	4,33 €

Dimensions in mm

Altri prodotti...


PRF1945

Profilato alluminio standard, 19 x 45 mm


PP50

Riduttore a ruota e vite senza fine, da 6.50 a 12.80 Nm


SEH

Attrezzo di bloccaggio a tirante, A tirante - acciaio


RAGFLOWsupport

Accessori per rotaia a rulli Floway2®, Roller track support


ZBconique

Ingranaggio conico in plastica, 1:1


SH1

Ingranaggio elicoidale ad assi paralleli, Plastica lavorata (delrin)


RPCplss

Ruota girevole a doppio bloccaggio, Inox - poliammide


F7-SF-SM

Visualizzatore multifunzione, Supporto - montaggio frontale


PRF_FIX_ANG

Fissaggio, Fissaggio angolare


PRES2HR

Pressa manuale da banco, Pressione fino


LRM

Dado cilindrico in bronzo, Bronzo - 1


FF40

Riduttore ad alberi paralleli, da 59 a 210

Prodotti correlati


PRF4545

Profilato alluminio standard, 45 x 45 mm