Fastening pin with ring

AFA


Steel

- **Ball pin**
- Quick and easy assembly of workpieces and other elements
- Double shear force (F) = S x τAB max
- Materials:
  Body - Chromed steel
  Ring - Stainless steel




Advantages

- These fastening pins with rings are an economic alternative to interlocking safety fasteners.
- They are easier to use and cheaper than a BAB ball pin but offer a lower level of safety



Typical application



DISCOUNTS

Qty	1+	6+	10+	25+
Disc.	List	-5%	-10%	On request

Part number	ØD	ØD1	ØD2	L	L1	Double shear strength (kN)	Stock*	Price each 1 to 5
AFA6-15	23	6	6,5	15	7	22	✔	6,40 €
AFA6-20	23	6	6,5	20	7	22	-	6,53 €
AFA6-30	23	6	6,5	30	7	22	✔	6,69 €
AFA6-40	23	6	6,5	40	7	22	✔	6,87 €
AFA8-30	28	8	8,8	30	8	28	✔	6,69 €
AFA8-40	28	8	8,8	40	8	28	✔	6,87 €
AFA8-50	28	8	8,8	50	8	28	✔	7,10 €

Dimensions in mm

Altri prodotti...



Ruota girevole a foro centrale, Poliuretano - Mozzo alluminio (Ultra...



Anello di sollevamento, a 45° a saldare



Cinghia aperta al metro tipo RPP, RPP8 Poliuretano armatura in acciaio



Volantino a 6 lobi, Duroplast - Inox



Riduttore a rinvio angolare, da 0.60 a 3.84 Nm



Flexible drive shaft, Masterflex® Steel, with PVC casing



Cerniera a molla, saldabile



Piastra di giunzione per cinghia RPP, RPP14



Catena semplice al metro, Acciaio



Manicotto chiuso a sfere inox di precisione, Di



Ingranaggio conico - Acciaio C43 - ECO, 4:1



Grano punta in ottone, punta in ottone

Prodotti correlati



Perno di fissaggio, con chiusura a scatto



Copiglia a scatto, A scatto



Copiglia per tubo, Clip per tubo



Perno autobloccante a sfere, Inox temprato