

Welded lifting ring for straight lifts

ASH

Steel


- **Weldable lifting ring**
- Marked with CE symbol, CMU and manufacturer's ref
- **Material:**
Black unfinished steel

Assembly


- Installation instructions available on request
- Welding should be done in accordance with DIN 5817 (section 15 429) by an operator qualified to EN287-1

Info.

- The breaking load is obtained by multiplying the SWL by a factor of safety of 5.



Typical application



DISCOUNTS

Qty	1+	6+	20+	50+
Disc.	List	-10%	-20%	On request

Part number	CMU (kg)	ØT	ØA	B	C	D	Weight (kg)	Stock*	Price each 1 to 5
ASH24-200	200	9	24	43	10	54	0,06	✓	2,22 €
ASH31-500	500	12	31	55	12	68	0,14	✓	3,18 €
ASH43-1000	1000	13	43	67	12	85	0,18	✓	4,77 €
ASH48-2000	2000	18	48	82	16	105	0,40	✓	7,41 €
ASH57-3000	3000	21	57	95	17	128	0,66	-	14,12 €
ASH67-4000	4000	25	67	107	15	148	1,02	-	26,87 €
ASH82-6000	6000	28	82	135	24	189	1,92	-	83,48 €
ASH100-8000	8000	30	100	165	35	210	3,12	-	87,69 €

Dimensions in mm


Altri prodotti...



PSG3
Ingranaggio dritto di precisione, Acciaio 35NCD6 pretrattato



PR105
Piede fissabile con snodo - poliammide, Ø 103



PM4
Coppia ruota e vite senza fine, Plastica lavorata (delrin)



RFK28B
Riduttore ipoide inox, fino a 130 Nm



HLA24
Rinvio angolare a dentatura spiroidale, Fino a 78Nm



PRS100
Piede snodabile tutto inox Ø100, Ø 100



DBL805
Rotella per catena, Serie 805



CHA1056_U4
Cerniera ad avvitare, Sezione 40X40



BPMc
Pressore a molla con intaglio e puntale a sfera, Corpo inox 303



BPPL
Mini sfera portante a incastro, A incastro



DOMI50
Kit di raccordo, Kit di raccordo XZ



RPCplss
Ruota girevole con piastra, Inox - Poliammide

Prodotti correlati



VRBS
Anello di sollevamento, Articolato - a saldare



VLBS
Anello di sollevamento, Articolato - a saldare



VASL
Anello di sollevamento, a 45° a saldare