

# Welded lifting ring for straight lifts

## ASH

## Steel


- **Weldable lifting ring**
- Marked with CE symbol, CMU and manufacturer's ref
- **Material:**  
Black unfinished steel

### Assembly


- Installation instructions available on request
- Welding should be done in accordance with DIN 5817 (section 15 429) by an operator qualified to EN287-1

### Info.

- The breaking load is obtained by multiplying the SWL by a factor of safety of 5.



Typical application



### DISCOUNTS

Qty	1+	6+	20+	50+
Disc.	List	-10%	-20%	On request

Part number	CMU (kg)	ØT	ØA	B	C	D	Weight (kg)	Stock*	Price each 1 to 5
ASH24-200	200	9	24	43	10	54	0,06	✓	2,22 €
ASH31-500	500	12	31	55	12	68	0,14	✓	3,18 €
ASH43-1000	1000	13	43	67	12	85	0,18	✓	4,77 €
ASH48-2000	2000	18	48	82	16	105	0,40	✓	7,41 €
ASH57-3000	3000	21	57	95	17	128	0,66	-	14,12 €
ASH67-4000	4000	25	67	107	15	148	1,02	-	26,87 €
ASH82-6000	6000	28	82	135	24	189	1,92	-	83,48 €
ASH100-8000	8000	30	100	165	35	210	3,12	-	87,69 €

Dimensions in mm

## Altri prodotti...



VELM6

Supporto avvitabile per rotolo a strappo fermacavi, Poliammide



PSG125S

Ingranaggio dritto di precisione, Inox 303



PR881

Ruota di rinvio, Serie 881



TBE12

Economic mini-table with trapezoidal leadscrew, 2kg



Q7

Cuscinetto obliquo a sfere, Acciaio



Gdal

Giunto cardanico doppio serie eco, Sollecitazioni leggere



DZYSS

Piedino antivibrante cilindrico inox, inox



HRV

Sistema di guida su binario a V Simple Select®, Binario con carrello



EMAS

Antistatic knurled nut, Antistatic



PARF80

Piede senza snodo, Piede snodato oscillante fissabile Ø80



INS\_SS

Inserto auto-filettante, Inox 316



NT61

Riduttore coassiale a treni paralleli, da 5 a 14 Nm - a treni parall...

## Prodotti correlati



VRBS

Anello di sollevamento, Articolato - a saldare



VLBS

Anello di sollevamento, Articolato - a saldare



VSL

Anello di sollevamento, a 45° a saldare