Support arm

Two axes of rotation


BDP2R


- ***Universal adjustable support arm, strengthened***
- *Material :*
  Aluminium with steel screws

Advantages

- *Safe in operation through use of optimised jaw support*

NEW !






DISCOUNTS

Qty	1+	10+	30+
Disc.	List	-5%	On request

Part number	ØA	B	ØC	D	L	M	⍁F	N	P	Weight (g)	Price each 1 to 9
BDP20-50/2R	20	19	20	43	50	59	24	47	16,5	89	90,27 €
BDP20-100/2R	20	19	20	43	100	59	24	47	16,5	104	95,80 €
BDP20-150/2R	20	19	20	43	150	59	24	47	16,5	119	101,32 €

Dimensions in mm

Altri prodotti...



Ruote per viti senza fine , Plastica lavorata (delrin)



Tavola di posizionamento a passo inverso manuale, 2kg




Manovella ad impugnatura girevole, Alesaggio quadrato



Fissaggio, Fissaggio standard



Sistema di guida su binario a V Simple Select®, Binario con carrello



Panel accessories, Guarnizione - Ø 6mm



Staffa di montaggio per molla a gas, Staffa di montaggio a squadra p...



Puleggia folle, Per cinghia tonda




Manopola a pressione, PVC nero



Riduttore coassiale a treni paralleli, da 20 a



Chiusura a leva regolabile, Corsa da



Copiglia beta, Beta

Prodotti correlati



Braccio di reazione, Rigido



Braccio di reazione, Serraggio standard