

Miniature indexing button

For reduced spaces

BIM

Miniature

- Particularly suitable for screwing into thin-walled parts.
- Works well in reduced spaces
- Non-removable spaces
- Materials:
Head - matt thermoplastic
Body - galvanised steel or 303 stainless steel
Pin - 303 stainless steel





Assembly

- Screw in as far as possible, then pull on the button to reveal the hexagonal nut for final assembly.

Operation

- For the locking version, the button is pulled and then turned 90° where it is retained in a notch.
- Working temperature range -30°C to 80°C



DISCOUNTS

Qty	1+	6+	20+
Disc	List	-10%	On request

Part number	ØD1	ØD2	L1	ØD3	ØD4	L2	L3	L4	SW	F1 (N)	F2 (N)	Weight (g)	Stock*	Price each 1 to 5
Non-locking version														
BIM4-8-26.5	4	M8x0,75	26,5	21,0	15,0	5	5	3,5	10	4,5	12	14	✓	7,99 €
BIM5-8-26.5	5	M8x0,75	26,5	21,0	15,0	5	5	3,5	10	4,5	12	14	✓	8,21 €
BIM6-10-34	6	M10x1	34	25,0	18,0	7	7	4,5	12	5	18	25	✓	9,65 €
BIM7-10-34	7	M10x1	34	25,0	18,0	7	7	4,5	12	5	18	26	-	10,13 €
Locking version														
BIM4-8-26.5/LOK	4	M8x0,75	26,5	21,0	15,0	5	5	3,5	10	4,5	12	13	✓	7,99 €
BIM5-8-26.5/LOK	5	M8x0,75	26,5	21,0	15,0	5	5	3,5	10	4,5	12	14	-	8,21 €
BIM6-10-34/LOK	6	M10x1	34	25,0	18,0	7	7	4,5	12	5	18	24	-	9,65 €
BIM7-10-34/LOK	7	M10x1	34	25,0	18,0	7	7	4,5	12	5	18	25	-	10,13 €

Dimensions in mm

0 825 88 6000
Service 0,15 € / min
+ prix appel

cial2@hpceurope.com

HPC

SUPPLEMENT 2019

137

Altri prodotti...



TBE12

Economic mini-table
with trapezoidal
leadscrew, 2kg



CHA1056_U20

Cerniera ad avvitare,
Sezione 76x50



PRES2HR

Pressa manuale da
banco, Pressione fino
a 200kg



SUPss

Calettatore di
bloccaggio
autocentrante inox,
Senza ghiera




PPRss

Piastrina con anello,
Inox



PTMR

Telescopico furniture
foot, threaded stud



CFC

Pressore a molla con
esagono incassato, A
contatto elettrico




NSA

Connettore rinvio
d'angolo, Articolato




GCB880

Guida curva, Serie
880 e 881



CAB

Cavo di fissaggio, Inox



RPP14

Cinghia di
trasmissione RPP,
RPP14



INO

Ingranaggio interno,
Plastica lavorata
(delrin)

Prodotti correlati



BIMSS

Pistoncino a molla,
Miniatura inox



PPD

Pistoncino a molla,
Per lamiera



PPF

Pistoncino a molla,
con flangia



SLBW

Pistoncino a molla, Da
saldare - Acciaio