

Miniature indexing button

For reduced spaces

BIM

Miniature

- Particularly suitable for screwing into thin-walled parts.
- Works well in reduced spaces
- Non-removable spaces
- Materials:
Head - matt thermoplastic
Body - galvanised steel or 303 stainless steel
Pin - 303 stainless steel





Assembly

- Screw in as far as possible, then pull on the button to reveal the hexagonal nut for final assembly.

Operation

- For the locking version, the button is pulled and then turned 90°C where it is retained in a notch.
- Working temperature range -30°C to 80°C



DISCOUNTS

Qty	1+	6+	20+
Disc	List	-10%	On request

Part number	ØD1	ØD2	L1	ØD3	ØD4	L2	L3	L4	SW	F1 (N)	F2 (N)	Weight (g)	Stock*	Price each 1 to 5
Non-locking version														
BIM4-8-26.5	4	M8x0,75	26,5	21,0	15,0	5	5	3,5	10	4,5	12	14	✓	7,99 €
BIM5-8-26.5	5	M8x0,75	26,5	21,0	15,0	5	5	3,5	10	4,5	12	14	✓	8,21 €
BIM6-10-34	6	M10x1	34	25,0	18,0	7	7	4,5	12	5	18	25	✓	9,65 €
BIM7-10-34	7	M10x1	34	25,0	18,0	7	7	4,5	12	5	18	26	-	10,13 €
Locking version														
BIM4-8-26.5/LOK	4	M8x0,75	26,5	21,0	15,0	5	5	3,5	10	4,5	12	13	✓	7,99 €
BIM5-8-26.5/LOK	5	M8x0,75	26,5	21,0	15,0	5	5	3,5	10	4,5	12	14	-	8,21 €
BIM6-10-34/LOK	6	M10x1	34	25,0	18,0	7	7	4,5	12	5	18	24	-	9,65 €
BIM7-10-34/LOK	7	M10x1	34	25,0	18,0	7	7	4,5	12	5	18	25	-	10,13 €

Dimensions in mm

0 825 88 6000
Service 0,15 € / min
+ prix appel

cial2@hpceurope.com

HPC

SUPPLEMENT 2019

137

Altri prodotti...



PRF4545
 Profilato inox standard, 45 x 45 mm



CM
 Tools Hygienic Usit® and Hygienic Design®, Combination spanner



DH
 Spina cilindrica, standard DIN 6325




STL2108
 Spazzola a listello, 8mm slots



PSG35
 Ingranaggio dritto di precisione, Inox 316



AT10courroie
 Cinghia chiusa, AT10 Poliuretano armatura in acciaio



T5courroie
 Cinghia chiusa, T5 Poliuretano armatura in acciaio



MFB_MHB
 Ingranaggio conico in plastica stampata (nylon), 1.5:1



HTD8M_30
 Puleggia HTD per cinghia RPP, HTD8 Ghisa



D-PAR_SS
 Piedino antivibrante, inox



PV1R
 Braccio portaventosa orientabile, Serraggio standard



ZDB
 Ingranaggio conico plastica lavorata (delrin), 2:1

Prodotti correlati



BIMSS
 Pistoncino a molla, Miniatura inox



PPD
 Pistoncino a molla, Per lamiera



PPF
 Pistoncino a molla, con flangia



SLBW
 Pistoncino a molla, Da saldare - Acciaio