
Right angled gearbox, double output shafts

BLHM70


Torque up to 128Nm

- ***The two outputs rotate in opposite directions***
- Ratios of 1:1 to 2:1
- Output backlash ≃1°
- Max. speed: 4000 rpm
- Materials: casing: anodised aluminium
  input: hardened steel,
  output: hardened steel
- Weight: 8.76 kg



Options

- Can be modified to your specifications



Output torque Nm (NM values given as a guide only)

Ratios		1:1	2:1
INPUT SPEED (rpm)	3000	43	26
	2000	47	30
	1000	51	34
	500	64	38
	100	85	51
	50	94	60
	10	128	77

Innovative ! Outputs rotate in different directions

DISCOUNTS

Qty.	1+	2+	4+	6+
Disc.	List	-15%	-20%	On request

Part number	Ratio	Efficiency at 1000 rpm	Max. input speed (rpm)	Max. output speed (rpm)	Module	Price each
BLHM70-1	1:1	88%	3000	3000	4,0	2 152,92 €
BLHM70-2	2:1	88%	3000	1500	2,5	2 152,92 €


Dimensions in mm

Altri prodotti...



PPCss

Piastrina con anello, Inox



PCF2

Supporto antivibrante cabina conico, Piastra a base ovale



DEP

Attrezzi Hygienic Usit® and Hygienic Design®, Bussole per il monta...



CMM

Testa a snodo maschio DIN ISO12240-4, Acciaio / bronzo



PTA150

Piede snodato con base stampata Ø150, 40000N



SBS_L

Giunzione per catena al metro, Falsa maglia - inox



DOMI50

Kit di raccordo, Kit di raccordo XZ



SVR30

Martinetto a vite - Vite rotante, Con madrevite esterna



PDD

Pressore a molla sensore di rilevamento, Con asta di comando per int...



PR40

Piede fissabile con snodo - poliammide, Ø 40



SVT20

Martinetto a vite - Vite traslante, Vite traslante



HTD14M_55

Puleggia dentata di trasmissione tipo HTD, HTD14 Ghisa o Acciaio

Prodotti correlati



BLH70

Rinvio angolare a L, da 26 a 128 Nm



BLHT70

Rinvio angolare a T, da 26 a 128 Nm