Doorstop

BLOC

Plastic

- ***Element for square tube structure***
- *Material: reinforced polyamide*


Info.

- **Not sold individually, please contact us for details**

Accessories

- *Magnetic lock* **SER**
- *Hinge* **CHA**
- *Manual lock* **LOQ**







Typical application

DISCOUNTS

Qty.	1+	50+	100+
Disc.	List	-5%	On request

Part number	Weight (kg)	Stock*	Price each 1 to 49
BLOC-25	0,01	✔	4,03 €

**Depending on availability - Dimensions in mm*


Altri prodotti...


PTA50

Piede snodato con base stampata Ø50, 4000N


RTT

Calettatore di bloccaggio, Coppia media/elevata


PCF2

Supporto antivibrante cabina conico, Piastra a base ovale


CHA1056_U4

Cerniera ad avvitare, Sezione 40X40


MHPGR

Manovella ad impugnatura girevole,


CFF

Testa a snodo femmina DIN ISO12240-4, Acciaio / bronzo


T5courroie

Cinghia di posizionamento T, T5 Poliuretano armatura in acciaio


BABreceptacle

Perno autobloccante, Bussola di innesto


SVT20

Martinetto a vite - Vite traslante, Vite traslante


DPAR_DKON

Piedino antivibrante parabolico, Acciaio


FF40

Riduttore ad alberi paralleli, da 59 a 210


PF20

Riduttore a ruota e vite senza fine, fino a 5 Nm

Prodotti correlati


CHA135

Cerniera ad avvitare, 135 gradi


LOQ

Accessori per porte, Fermaporte a scatto