

# Box set of hose clamps

## BOX-CS

## Steel

- Boxes containing solid 9 and 12mm wide hose clamps
- Ideal for the maintenance department

### Info.

- Also contains a flexible screwdriver



### Small version BOX-CS-100

Quantity	Range of adjustment Ø	Collar width
15	8-12	9
20	10-16	9
20	12-22	9
15	16-27	9
15	20-32	9
15	25-40	9

### Large version BOX-CS-220

Quantity	Range of adjustment Ø	Collar width
20	8-12	9
25	10-16	9
30	12-22	9
25	16-27	9
25	20-32	9
25	25-40	9
20	16-27	12
20	20-32	12
20	32-50	12
10	40-60	12

### DISCOUNTS

Qty	1+	2+	5+
Disc.	Prix	-5%	On request

Part N°	Box dimensions	Quantity per box	Price each
BOX-CS-100	255x315x65	100 clamps	59,84 €
BOX-CS-220	460x360x85	220 clamps	124,68 €

All dimensions in mm

## Altri prodotti...



G01  
Giunto cardanico  
semplice,  
Sollecitazioni normale



NKIB  
Cuscinetto combinato  
con anello interno,  
Carico assiale  
bidirezionale



SSB  
Ingranaggio conico  
inox, 1:1



SVG  
Chiusura a leva  
regolabile, Corsa da  
82mm a 92mm



COA-COG  
Staffa di montaggio  
per molla a gas,  
Staffa di montaggio  
piana per s...



RGS  
Giunto senza gioco  
Rotex® GS, da 0.5 a  
190Nm



HSE-HSB  
Distanziatore  
esagonale, Ottone



LRH  
Vite trapezoidale a  
doppia inclinazione, a  
doppia inclinazione - 1  
f...



PLM-C  
Magnetone piatto di  
fermo, Magnetone di



CLB\_T  
Maniglia a ripresa,  
Zamak



PO  
Maniglia a ponte -  
Multi-settore, Foro



HW\_HT  
Guida su semi-binari,  
Ruota

## Prodotti correlati



BOX-CSss  
Fascette di serraggio,  
Valigetta di fascette  
inox