Box sets of self-locking nuts DIN985

BOX-NINA

Steel

- Boxes of standard DIN985 self-locking nuts

Application

- Ideal for the maintenance department or for use in workshops





- Box details

Quantity	Thread ØM	Thread
Standard thread		
100	M4	0,70
100	M5	0,80
100	M6	1,00
50	M8	1,25
50	M10	1,50
25	M12	1,75
10	M14	2,00
10	M16	2,00
Fine thread		
50	M10	1,00
25	M12	1,50
20	M14	1,50
10	M16	1,50

DISCOUNTS

Qty	1+	2+	5+
Disc.	Prix	-5%	On request

Part N°	Quantity per box	Price each
BOX-NINA	550 washers	75,50 €

Altri prodotti...



RFK38C

Riduttore ipoide inox, fino a 200 Nm



HLA19

Rinvio angolare a dentatura spiroidale, Fino a 43Nm



NPCR

Morsetto porta fotocellule, Regolabile



GAL_25

Rullo per trasportatore, Senza cuscinetti a sfere



OP3_14_06

Accessorio per indicatori, Boccola di riduzione



DOMI30

Slitta di regolazione Domino 30, Slitta DOMILINE 30 con contatore e ...



M1

Vite senza fine , Acciaio temprato



PTGP

Puleggia folle, Per cinghia piatta



DPAR_DKON

Piedino antivibrante parabolico, Acciaio



NTM

Grano punta in nylon, punta in nylon



SDA


Pistoncino a molla - Supporto, fissaggio parallelo alla serratura



HRV

Sistema di guida su binario a V Simple Select®, Binario con carrello

Prodotti correlati



NIN

Dado autofrenante , Acciaio



BOX-SHNA

Dado esagonale - DIN934, Valigetta di dadi acciaio



BOX-WM

Rondella semplice - DIN125, Valigetta di rondelle acciaio