O-Ring kit, NBR90Sh A

BOX-TOR-ORFS Sizes from 7.65x 1.78mm to 37.82x1.78mm

- **Selection of O-Rings for ORF fittings**
- **8 sizes**
- Material:
  Nitrile NBR 90 shore A
- Working temperature range: -30° to +110°C




Applications

Suitable for:
- Hydraulic fluids
- HFA fluids
- HFB fluids
- HFC fluids
- Air

Info

- Ideal for use in the maintenance dept.



Box contents

Quantity	ØD1	ØD2
25	7,65	1,78
25	9,25	1,78
25	12,42	1,78
25	15,60	1,78
20	18,77	1,78
15	23,52	1,78
10	29,87	1,78
10	37,82	1,78

DISCOUNTS

Qty	1+	3+	5+
Disc.	Net	-5%	On request

Part N°	Material	Qty per box	Price each
BOX-TOR-ORFS	NBR 90 Sh A	155 pieces	35,77 €

All dimensions in mm

Altri prodotti...


ZBconique

Ingranaggio conico in plastica, 1:1


HTD8M_30

Puleggia dentata di trasmissione tipo HTD, HTD8 Acciaio


MAX22

Motoriduttore DC 12V e 24V DC, da 0,07 a 0,2Nm


PRES3HR


Pressa manuale da banco, Pressione fino a 400kg


HSSss

Vite a spalla di precisione inox ISO7379, Inox ISO 7379


PTMR


Piede regolabile, threaded stud


GPBSS

Impugnatura sferica femmina filettata, Inox 304


BAC105

Contenitore a becco, 8mm


WJUM10

Pattino Drylin® W, Pattino


DILC

Indexing plunger with cam, with cam


MLY_SS

Grillo con chiodo ad occhiello, Inox


PRF_PL_4590

Elementi di giunzione, Piastra di giunzione - 45x90 mm

Prodotti correlati


BOX-TOR-TOOL

Valigetta di guarnizioni toriche in nitrile, Extraction tools