

Pressed stainless steel bearing for light loads

BPFSS

Flange with 3 mounting holes

- Pressed sheet steel housing
- Material: stainless steel


NEW:
stainless steel
range

Application

- Mounting a simple bearing, suitable for light loads only



stainless
steel



DISCOUNTS

Qty	1+	6+	20+	40+	60+
Disc.	List	-10%	-15%	-20%	On request

Part number	ØD	A	E	T	M	S	F	Bolt size	B1	N	Weight (kg)	Stock*	Price each 1 to 5
BPF204/SS	20	90	71	2	16	9	56	M8	25	7	0,29	✓	19,50 €
BPF205/SS	25	95	76	2	18	9	60	M8	27	7,5	0,34	✓	24,32 €
BPF206/SS	30	113	90	2,6	18	11	71	M8	30	8	0,55	✓	13,79 €
BPF207/SS	35	122	100	2,6	20	11	81	M10	32	8,5	0,69	-	18,17 €

Dimensions in mm

Altri prodotti...



BPL

Sfera portante con flangia, Leggero



BGC

Giunto Oldham, con ganascia di serraggio




VTLF

Volantino a 3 lobi, Poliammide - Ottone



LVT

Mini martinetto motorizzato 1A, 1 ampere



P20

Riduttore a ruota e vite senza fine, fino a 5 Nm



PRF-SCREEN-5

Screen support, Support with 5 axes of rotation



CHT

Motore AC asincrono trifase, 0.18 a 0.55kW



ZBconique

Ingranaggio conico in plastica, 1:1



E15

Riduttore a rinvio angolare, da 0.40 a 5 Nm



HD

Giunto cardanico doppio ad aghi, da 0.40 a 5 Nm



GLB

Volantino a 6 lobi filettato, da 0.40 a 5 Nm



SCE

Serracavo, Acciaio

Prodotti correlati



BPPss

Supporto ritto in lamiera con cuscinetto inox, Inox



BPFLss

Supporto a flangia ovale a carico leggero inox, Inox



BPF

Supporto a flangia tonda con cuscinetto, Lamiera



UCF_SS

Cuscinetto a flangia quadrata tutto inox, Inox