

# Flush fitting ball transfer unit with flange

## BPHF

## For heavy loads

- Carrying ball for handling solid body
- For heavy loads
- Machined bodies and covers
- Lubricated for life
- Orientation: horizontal with ball upwards
- Unique drainage hole
- Max. speed: 1.5m/s
- Working temperature range: -30 to +100°C
- Materials:

**BPHF:**galvanised steel body and chromed steel ball

**BPHF/AS:**galvanised steel body and 420 stainless steel balls

**BPHF/SS:**body, components and balls- 420 stainless steels




### Accessoires

- BPHFCLIP mounting clip

### Advantages

- Good resistance to shocks
- Optional clips compensate for irregularities in seat bore diameter




### DISCOUNTS

Qty	1+	6+	20+	40+	60+
Disc.	Net	-10%	-15%	-20%	On request

Part N°	Ødwb ball	ØA	B	C	ØD	E	Carrying capacity (kg)	Weight (g)	Price each 1 to 5
<b>Steel body, steel balls</b>									
BPHF15-24	15	24	9,5	4,0	31	21,0	60	0,059	4,96 €
BPHF22-36	22	36	9,8	3,8	45	30,5	180	0,189	9,68 €
BPHF30-45	30	45	13,8	5,8	55	36,8	350	0,360	15,32 €
BPHF45-62	45	62	19,0	9,0	75	53,5	600	1,010	49,56 €
<b>Steel body, stainless steel balls</b>									
BPHF15-24/AS	15	24	9,5	4,0	31	21,0	50	0,059	6,18 €
BPHF22-36/AS	22	36	9,8	3,8	45	30,5	180	0,188	10,72 €
BPHF30-45/AS	30	45	13,8	5,8	55	36,8	350	0,357	18,79 €
BPHF45-62/AS	45	62	19,0	9,0	75	53,5	600	1,000	65,24 €
<b>Stainless steel body, stainless steel balls</b>									
BPHF15-24/SS	15	24	9,5	4,0	31	21,0	40	0,058	16,90 €
BPHF22-36/SS	22	36	9,8	3,8	45	30,5	126	0,188	40,04 €
BPHF30-45/SS	30	45	13,8	5,8	55	36,8	220	0,357	53,68 €
BPHF45-62/SS	45	62	19,0	9,0	75	53,5	350	1,020	132,12 €

All dimensions in mm

## Altri prodotti...



MO

Coppia ruota e vite senza fine , Plastica lavorata (delrin)



FBL4004\_K32

Spazzola al metro, Polipropilene nero striato (PP)



ZBconique

Ingranaggio conico in plastica, 1:1



J64

Riduttore coassiale a treni paralleli, da 0.57 a 2.25 Nm - a treni p...



CHT

Motore AC asincrono trifase, 0.12 a 0.22kW



LVT

Mini martinetto motorizzato 2A, 2 ampere



EIM

Cavallotto Inox, Inox



BABA

Perno autobloccante, Acciaio



T5\_11

Puleggia dentata di posizionamento tipo T, T5 alluminio



COA-COG

Staffa di montaggio per molla a gas, Staffa di montaggio



CHINV2

Cerniera invisibile, Invisibile - Apertura fino a 125°



PDR-RD

Piede con ruota integrata, Ruota dissaccata

## Prodotti correlati



BPHF

Sfera portante a incastro con flangia, Forte



BPHF

Sfera portante a incastro con flangia, Forte



BPPE

Sfera portante, Leggero



BPLE

Sfera portante a incastro, Leggero