

Flange mounting ball transfer unit


Plastic

BPPE

- **Plastic ball mounting ball transfer unit**
- Push fit for rapid installation & replacement where only single-sided access to the mounting surface is available
- Clips compensate for irregularities in seat bore diameter
- Max. speed: 1m/s
- Working temperature range: -20 to +70°C
- Materials:
Acetal body and balls (POM)

Advantages

- Resists salt water and chemical attacks
- Non-conductive and non-magnetic
- Suitable for antimicrobial applications
- For use in chemical, pharmaceutical and medical applications



DISCOUNTS

Qty	1+	6+	20+	40+	60+
Disc.	Net	-10%	-15%	-20%	On request

Part N°	Ødw ball	ØA	B	C	ØD	E	Carrying capacity (kg)	Weight (g)	Price each 1 to 5
BPPE15-24/PP	15	24	8,0	4,8	30	20,0	7	0,010	18,29 €
BPPE22-36/PP	22	36	9,8	4,5	45	30,5	10	0,035	27,43 €
BPPE30-45/PP	30	45	13,8	5,8	55	37,0	15	0,065	32,65 €
BPPE45-62/PP	45	62	19,0	8,5	75	53,5	20	0,182	72,36 €

All dimensions in mm

0 825 88 6000
Service 0,15 € / min
+ prix appel

Fax

cial2@hpceurope.com

HPC

SUPPLEMENT 2019

255

Altri prodotti...



Barra dentata, AT10



Motoriduttore AC asincrono da 0,18 a 0,55kW, 0.18 a 0.55kW



Boccola di fermo per perno ad innesto, Acciaio nichelato



Ingranaggio dritto di precisione, Inox 303



Pignone a catena - acciaio, 6mm (DIN 04-1)



Cremagliera a sezione circolare, Inox - modulo 1-5




Rinvio angolare ad albero cavo, fino a 10.3 Nm



Volantino pieno con impugnatura girevole, Inox 304



Riduttore a rinvio angolare, da 4.50 a 24 Nm



Tenditore per catena automatico, Con pattino 180°



Pistoncino a molla, acciaio classe 5.8



Riduttore a rinvio angolare, da 1.50 a 9 Nm

Prodotti correlati



Sfera portante, Anello di fissaggio - montaggio dall'alto



Sfera portante a incastro, Leggero



Sfera portante a incastro con flangia, Forte



Sfera portante, Forte