Ball transfer unit in blue certified plastic

Suitable for foodstuff sector


BPPEBLU


- ***The ball transfer units are made of a certified blue plastic which is suitable for use in the foodstuff sector***
- *Press-in assembly*
- *Conveying speed up to 1.5 m/s*
- *Foodstuff conform: Food Grade, EU Regulation 1935/2004, EU Regulation 10/2011*
- *Material :*
  - *Housing and cap POM*
  - *Bearing ball stainless steel*
  - *Load ball stainless steel or plastic*
- *Temperature range: -30 °C to +50 °C (up to +30°C with plastic load balls)*



Advantages

- *The ball transfer units are equipped with a gap-free and sealed cap, which prevents the formation of soiled edge*
- *The dirt holes underneath the housing enable particularly easy cleaning of the ball transfer units*





DISCOUNTS

Qty	1+	6+	20+	30+
Disc.	List	-10%	-15%	On request

Part number	ØD	ØD1	ØDK	H	H1	H2	Load rating C (kg)	Price each 1 to 5
Load ball in POM								
BPPE15-24/PP/BLU	24±0,1	31±0,2	15,875	20,5±0,2	9,5±0,2	4,5	20	
BPPE22-36/PP/BLU	36±0,1	45±0,2	22,225	30,5±0,2	10±0,2	4,5	25	
BPPE30-45/PP/BLU	45±0,1	55±0,1	30,000	37±0,1	14±0,1	5,5	35	
BPPE45-62/PP/BLU	62±0,1	75±0,1	44,500	53,5±0,1	19±0,1	9,0	50	
Load ball in stainless steel								
BPPE15-24/SS/BLU	24±0,1	31±0,2	15,875	20,5±0,2	9,5±0,2	4,5	20	
BPPE22-36/SS/BLU	36±0,1	45±0,2	22,225	30,5±0,2	10±0,2	4,5	25	
BPPE30-45/SS/BLU	45±0,1	55±0,1	30,000	37±0,1	14±0,1	5,5	35	
BPPE45-62/SS/BLU	62±0,1	75±0,1	44,500	53,5±0,1	19±0,1	9,0	50	

All dimensions in mm.

Tel. +(39) 011 760 95 05 **info2@ctmeca.com**

HPC Ct Meca

Novembre 2025

Altri prodotti...



Guida su semi-binari, Binario



Ingranaggio conico - Acciaio C43 - ECO, 3:1



Kit di raccordo, Kit di raccordo XZ



Accessori per pannello, Blocco di fissaggio



Riduttore a ruota e vite senza fine, fino a 57 Nm



Rinvio angolare ad albero cavo, fino a 4.47 Nm



Tenditore per catena automatico, Con pignone acciaio



Puleggia dentata di posizionamento tipo T, T5 alluminio



Sistema di chiusura, Battuta a calamita



Puleggia folle, Per cinghia trapezoidale



Riduttore a ruota e vite senza fine, Albero semplice in uscita per



Mini martinetto motorizzato 4A, 4 ampere

Prodotti correlati



Sfera portante, Leggero



Sfera portante a incastro, Leggero



Sfera portante a incastro, Leggero



Sfera portante a incastro con flangia, Forte