Adjustable screw stop

Steel


BVR


- **Allows to easily create a stop that is adjustable over a 50mm range**
- Material:
  Burnished treated steel




Application

- Can be adjusted over the full range
- Final position is locked using a counter-nut.





Travel stop



DISCOUNTS

Qty	1+	6+	15+	20+
Disc.	List	-5%	-10%	On request

Part number	A	B	C	D	E	ØF	Price each 1 to 5
BVR6-30-30	30	44	37	30	10	M6	19,88 €
BVR8-40-40	40	56	48	40	13	M8	25,81 €
BVR10-50-50	50	70	60	50	17	M10	30,28 €
BVR12-60-60	60	84	72	60	19	M12	39,24 €
BVR16-80-80	80	112	96	80	24	M16	60,02 €

Dimensions in mm

Altri prodotti...


TM_CTM_CTF

Accessori per ventosa, Inserto per ventosa - A scatto


RPCplss

Ruota girevole con piastra, Inox - Poliammide


CLB_M


Maniglia a ripresa, Zamak


TCXR

Tenditore per catena automatico, Con pignone inox


DZYSS

Piedino antivibrante cilindrico inox, inox


PCF2


Supporto antivibrante cabina conico, Piastra a base ovale


DFG

Ventosa, silicone


CHB


Riduttore a ruota e vite senza fine, fino a 41 Nm


T0

Molla di torsione, Inox


T2

Cinghia di posizionamento T, T2.5 Poliuretano


WJUM16

Pattino Drylin® W, Pattino


SKM

Dado esagonale in acciaio, Acciaio - 1 filetto

Prodotti correlati