
Side flexing wide plate chain

CAP882T

Range 882 TAB

- ***Bending radius allows chain to follow a curved path***
- *Materials:*
  Plates: self lubricating brown acetal
  Pin: stainless steel 304
- *Operating temp.: -40°C to +85°C (+70°C in humid environments)*
- *Length 3048mm (80 plates)*




Advantages

- *Special shape prevents products being carried moving or falling whilst on curves*

Associated products

- *Drive sprocket* **PT882**
- *Idler sprocket* **PR882**



Typical application

DISCOUNTS

Qty.	1+	5+	10+
Disc.	List	-5%	On request

Part number	Width K (mm)	Length (mm)	Bend radius RM (mm)	Breaking load (N)	Weight (kg/m)	Price each 1 to 4
CAP882T-190	190,5	3048	610	8000	2,43	284,83 €
CAP882T-254	254,0	3048	610	8000	2,87	296,96 €
CAP882T-304	304,8	3048	610	8000	3,41	325,33 €

Dimensions in mm

Altri prodotti...



Cinghia aperta al metro tipo AT, AT5 Poliuretano armatura in acciaio



Ingranaggio conico in plastica, 1:1




Contenitore a becco, Aggancio orientabile



Ingranaggio conico in plastica stampata, 4:1



Dado trapezoidale, Polimero (Iglidur®) - 1 filetto



Ingranaggio conico - Acciaio 60C40, 1:1



Mini martinetto motorizzato 2A, 2 ampere



Cuscinetto a flangia quadrata in ghisa, Ghisa



Perno di bloccaggio tipo ¼ di giro, ¼ di giro



Accessori di collegamento, Kit di fissaggio



Chiusura a leva rigida ad anello, Standard



Aggancio per tirante chiusura in gomma, Aggancio

Prodotti correlati



Pignone di trazione, Serie 882



Ruota di rinvio, Serie 882