

12.7mm wide steel feeler strip on rolls

CLQ

Steel or stainless steel

- Rolls of precision feeler strip for adjusting, straightening, positioning or levelling

- Width 12.7mm

- Length per roll: 5 metres

(*except CLQ12-10-001 which is supplied on a 10 metre roll)

- Strip to be cut to form required

- Materials:

Steel 1.1274

Stainless steel 1.4310



steel or stainless steel

NEW!

Applications

- Aligning workpieces before machining


- Aligning differently sized/shaped pieces

- Adjusting valve lash

- Wedging tools

- Adjusting bearings

- Aligning a motor and a pump before coupling



Incorrectly aligned



Wedge adjustment


DISCOUNTS

Qty	1+	3+	5+
Disc.	List	-5%	On request

Part number		Thickness (mm)	Price each 1 to 2	
Steel	Stainless steel		Steel	S/Steel
CLQ12-10-001*	CLQ12-5-001/SS	0,01	93,68 €	51,24 €
CLQ12-5-002	CLQ12-5-002/SS	0,02	39,32 €	34,57 €
CLQ12-5-003	CLQ12-5-003/SS	0,03	15,97 €	17,87 €
CLQ12-5-004	CLQ12-5-004/SS	0,04	15,00 €	15,26 €
CLQ12-5-005	CLQ12-5-005/SS	0,05	14,31 €	12,87 €
CLQ12-5-006	CLQ12-5-006/SS	0,06	11,44 €	12,87 €
CLQ12-5-007	CLQ12-5-007/SS	0,07	10,72 €	12,87 €
CLQ12-5-008	CLQ12-5-008/SS	0,08	10,25 €	12,87 €
CLQ12-5-010	CLQ12-5-010/SS	0,10	9,77 €	11,68 €
CLQ12-5-015	CLQ12-5-015/SS	0,15	10,25 €	13,35 €
CLQ12-5-020	CLQ12-5-020/SS	0,20	10,50 €	14,06 €
CLQ12-5-025	CLQ12-5-025/SS	0,25	10,96 €	15,50 €
CLQ12-5-030	CLQ12-5-030/SS	0,30	10,72 €	16,10 €
CLQ12-5-040	CLQ12-5-040/SS	0,40	12,16 €	20,73 €
CLQ12-5-050	CLQ12-5-050/SS	0,50	11,91 €	22,16 €

Dimensions in mm

Altri prodotti...



PRF-GPA

Guide for aluminium profile, Parallel rails



PSG125HC

Ingran. dritto di precisione trattato skiving, Acciaio 20NCD2 cement...



BOX-TOR-H

Valigetta di guarnizioni toriche in nitrile, 3.00 x 2.00mm a 45.20 x...



BAGO

Anello di bloccaggio, Inox



UTKswrr

Guida lineare Utilitrack®, Profilo guida a V



HTD14M_85

Puleggia dentata di trasmissione tipo HTD, HTD14 Ghisa



HK

Accessorio di serraggio manuale, Serraggio manuale LRX



GE

Chiusura a leva, Standard



BLHB20

Rinvio angolare ad albero cavo, fino a



M1

Coppia ruota e vite senza fine, Plastica



VB

Volantino a 6 lobi, Duroplast - Inox



BMF

Manopola, Zigrinata - Cieco

Prodotti correlati



CLQassortiment

Cuscinetti a sfere - Accessorio, Spessori metallici centesimali