

12.7mm wide steel feeler strip on rolls

CLQ

Steel or stainless steel

- Rolls of precision feeler strip for adjusting, straightening, positioning or levelling

- Width 12.7mm

- Length per roll: 5 metres

(*except CLQ12-10-001 which is supplied on a 10 metre roll)

- Strip to be cut to form required

- Materials:

Steel 1.1274

Stainless steel 1.4310



steel or stainless steel

NEW!

Applications

- Aligning workpieces before machining


- Aligning differently sized/shaped pieces

- Adjusting valve lash


- Wedging tools

- Adjusting bearings

- Aligning a motor and a pump before coupling



Incorrectly aligned



Wedge adjustment

DISCOUNTS

Qty	1+	3+	5+
Disc.	List	-5%	On request

Part number		Thickness (mm)	Price each 1 to 2	
Steel	Stainless steel		Steel	S/Steel
CLQ12-10-001*	CLQ12-5-001/SS	0,01	93,68 €	51,24 €
CLQ12-5-002	CLQ12-5-002/SS	0,02	39,32 €	34,57 €
CLQ12-5-003	CLQ12-5-003/SS	0,03	15,97 €	17,87 €
CLQ12-5-004	CLQ12-5-004/SS	0,04	15,00 €	15,26 €
CLQ12-5-005	CLQ12-5-005/SS	0,05	14,31 €	12,87 €
CLQ12-5-006	CLQ12-5-006/SS	0,06	11,44 €	12,87 €
CLQ12-5-007	CLQ12-5-007/SS	0,07	10,72 €	12,87 €
CLQ12-5-008	CLQ12-5-008/SS	0,08	10,25 €	12,87 €
CLQ12-5-010	CLQ12-5-010/SS	0,10	9,77 €	11,68 €
CLQ12-5-015	CLQ12-5-015/SS	0,15	10,25 €	13,35 €
CLQ12-5-020	CLQ12-5-020/SS	0,20	10,50 €	14,06 €
CLQ12-5-025	CLQ12-5-025/SS	0,25	10,96 €	15,50 €
CLQ12-5-030	CLQ12-5-030/SS	0,30	10,72 €	16,10 €
CLQ12-5-040	CLQ12-5-040/SS	0,40	12,16 €	20,73 €
CLQ12-5-050	CLQ12-5-050/SS	0,50	11,91 €	22,16 €

Dimensions in mm

Altri prodotti...



RBNpl

Ruota girevole a doppio bloccaggio, Acciaio - caucciù



SC2

Giunto rigido in 2 parti, Ganascia di serraggio



NK17

Guida mini Drylin® N, Larghezza 17 mm



SSDB

Ingranaggio conico inox, 2:1



PSP

Accessori per pannello, Profilo supporto per pannelli



PTAf80-PAMF80

Piede fissabile con base lamiera Ø80, Ø 80



PTA100

Piede snodato con base stampata Ø100, Ø 100



VB

Volantino a 6 lobi, Duroplast - Ottone



PNA_R

Giunto elastico PERIFLEX, Collare di ricambio



M0

Coppia ruota e vite senza fine, Acciaio non temprato



GLT3-46

Guide telescopiche acciaio, Estensione totale



MBF

Manicotto filettato di bloccaggio, Montaggio e regolazione rapidi

Prodotti correlati



CLQassortiment

Cuscinetti a sfere - Accessorio, Spessori metallici centesimali