



Protective inserts for combination spanner

Hygienic Usit® and Hygienic Design® CMHDCO CMHDCF


- Protective inserts to be used with the CM combination spanner for mounting Hygienic Usit® and Hygienic Design® products

- Material:

Inserts: AlSi1MgMn

Advantages

- The protective caps have been specifically designed for fastening and un-fastening screwed connections with delicate surfaces.
- The protective caps will safely avoid the risk of contact corrosion with stainless steel screwed connections.
- The inserts are made of aluminium alloy EN AW 602 – a special aluminium suitable for contact with foodstuffs
- The protective cap is safely held in the spanner thanks to its special form and a sprung clip.



DISCOUNTS

Qty	1+	5+	10+
Disc.	Net	-5%	On request

Part N°	For spanner	SW	SW2	A1	B1	ØD1	ØD2	L1	T	T1	H	H1	Price each
													1 to 4
For open-ended spanner													
CM-10/HD/CF	CM-10/HD	10	7	9	17	2,3	-	19,4	5,6	-	8,6	-	18,84 €
CM-11/HD/CF	CM-11/HD	11	8	9	18	2,3	-	20,7	5,7	-	8,7	-	18,84 €
CM-13/HD/CF	CM-13/HD	13	10	10	22	3	-	23,2	6,7	-	10,7	-	19,05 €
CM-16/HD/CF	CM-16/HD	16	13	13	27	3	-	28,6	7,7	-	11,7	-	20,38 €
CM-19/HD/CF	CM-19/HD	19	16	13	30	4	-	32,5	8,6	-	12,6	-	21,54 €
CM-21/HD/CF	CM-21/HD	21	18	13	32	4	-	35,0	9,0	-	13,0	-	21,76 €
CM-27/HD/CF	CM-27/HD	27	24	14	40	4	-	43,8	10,8	-	15,0	-	23,26 €
For ring spanner													
CM-10/HD/CO	CM-10/HD	10	7	-	-	-	17	-	-	8,0	-	11,0	13,11 €
CM-11/HD/CO	CM-11/HD	11	8	-	-	-	18	-	-	9,4	-	11,4	13,11 €
CM-13/HD/CO	CM-13/HD	13	10	-	-	-	21	-	-	11,0	-	13,0	13,80 €
CM-16/HD/CO	CM-16/HD	16	13	-	-	-	25	-	-	12,4	-	14,4	14,15 €
CM-19/HD/CO	CM-19/HD	19	16	-	-	-	30	-	-	14,5	-	16,5	15,33 €
CM-21/HD/CO	CM-21/HD	21	18	-	-	-	32	-	-	14,7	-	16,7	15,43 €
CM-27/HD/CO	CM-27/HD	27	24	-	-	-	41	-	-	17,0	-	19,0	17,30 €

All dimensions in mm

0 825 88 6000

Service 0,15 € / min
+ prix appel

Fax


cial2@hpceurope.com

HPC


SUPPLEMENT 2019

63

Altri prodotti...



BTC
Tappo per tubo quadrato, Standard



MBrondele
Cuscinetti a sfere - Accessorio, Rondella di arresto MB



PSG35
Ingranaggio dritto di precisione, Inox 303



VTH
Vite a testa esagonale, Acciaio classe 8.8



ACA
Albero scanalato in acciaio, Acciaio



PSG25S
Ingranaggio dritto di precisione, Inox 316



BAG-MI
Anello di serraggio con intaglio e maniglia a leva, Acciaio



ERF
Terminale rapido per cavi, Terminale filettato



PF55
Riduttore a ruota e vite senza fine, fino a 57 Nm



SLBWSS
Pistoncino a molla, Da saldare - inox



GAL_42
Rullo per trasportatore, Senza cuscinetti a sfere



NSP
Morsetto base a 90°, Montaggio e regolazione rapidi

Prodotti correlati



CM
Attrezzi Hygienic Usit® and Hygienic Design®, Protective inserts f...



CM_CO
Attrezzi Hygienic Usit® and Hygienic Design®, Protective inserts f...