



- Self aligning bearing conforming to DIN ISO 12240-1, series E (DIN648)
- Housing: Stainless steel X6CrNiMoTi17-2-2 with a PTFE coating
- Ball: Stainless steel X105CrMo17, hardened and polished
- No lubrication required
- Operating temperature : -50° to +200°C

### Assembly

- Shaft tolerance g7
- Ball bore tolerance jS7

### Advantages

- Corrosion resistant and requiring no maintenance, these bearings are suitable for heavy duty applications




### DISCOUNTS

Qty.	1+	6+	20+	40+	60+
Disc.	Prix -10%	-15%	-20%	On request	

Part number	Tolerance (µm)	ØD	ØD1	ØD2 (h5)	A	B	Max. static load (kN)	Tilting angle α	Weight (g)	Stock*	Price each 1 to 5
CSS-06/SS	6	0/-8	8,0	14	4	6	9,0	13°	4	✓	39,47 €
CSS-08/SS	8	0/-8	10,2	16	5	8	15,6	15°	7	✓	26,28 €
CSS-10/SS	10	0/-8	13,2	19	6	9	23,4	12°	11	✓	34,26 €
CSS-12/SS	12	0/-8	14,9	22	7	10	32,0	11°	16	✓	35,96 €
CSS-15/SS	15	0/-8	18,4	26	9	12	50,0	8°	26	-	58,48 €
CSS-16/SS	16	0/-8	20,7	30	10	14	65,0	10°	49	✓	31,67 €
CSS-17/SS	17	0/-8	20,7	30	10	14	65,0	10°	38	-	67,06 €
CSS-20/SS	20	0/-10	24,2	35	12	16	90,5	9°	61	-	78,80 €
CSS-25/SS	25	0/-10	29,3	42	16	20	159,0	7°	110	-	92,76 €
CSS-30/SS	30	0/-10	34,2	47	18	22	197,0	6°	140	-	114,01 €

Dimensions in mm

## Altri prodotti...



T5courroie

Cinghia di  
posizionamento T, T5  
Poliuretano armatura  
in acciaio



ERT

Dado piastrina, Per  
scanalatura a T



GET-AL

Giunto elastico  
alluminio serie eco.,  
Alluminio



EHD06

Riduttore coassiale,  
da 8 a 19 Nm



LRRss

Interblocco di  
sicurezza, Chiusura a  
molla - inox



EHD16

Riduttore coassiale,  
da 210 a 380 Nm



PRF19\_E

Squadra di giunzione,  
PRF19 a PRF32



PSG15S

Ingranaggio dritto di  
precisione, Inox 316



PTAF80-PAMF80

Piede fissabile con  
base lamiera Ø80, Ø  
80



FBL6000\_K1

Spazzola al metro  
fibre PA6 da Ø0,2 a  
Ø0,3, Poliammide



PLC\_PLT

Magnete, Con foro  
maschiato



HTD8M\_20

Puleggia dentata di  
trasmissione tipo  
HTD, HTD8 Acciaio

## Prodotti correlati



CSS

Snodo sferico,  
acciaio/acciaio  
autolubrificante



SSE

Snodo sferico inox,  
Inox/PTFE