
★★ Motor-gearbox 12V and 24V DC


Torque from 12Nm to 15Nm — DOG258

- **Gearbox type: worm**
- Bearings: self-lubricating bushes
- Angular backlash: N/A
- Max. axial load: N/A
- Max. radial load: N/A
- Working temp.: -40°C to +80°C
- Weight: 3kg
- Ingress protection: IP53



Accessories

- Speed controler not available
- Servo amplifier **FIRSTDC -1Q-60/10**
- Power Supplies **ALIDR120-14,ALIDRP240-24**
- **HPC is unable to supply a speed controller for this motor gearbox**
- **The encoder cannot be mounted behind the motor.**



DISCOUNTS

Qty.	1+	6+	10+
Disc.	List	-7%	On request

Part number	Ratios	Unloaded speed (rpm)	Loaded speed (rpm)	Nominal torque (Nm)	Nominal current (mA)	Price each 1 to 5
12 V DC Version						
DOG258-12-50	52:1	50	40	12	12	403,65 €
DOG258-12-30	52:1	30	25	15	10	403,65 €
24 V DC Version						
DOG258-24-50	52:1	50	40	12	6	403,65 €
DOG258-24-30	52:1	30	25	15	5	403,65 €

Dimensions in mm

Altri prodotti...



G1

Ingranaggio dritto acciaio, Acciaio 20NCD2



NRV

Morsetto incrociato, Montaggio e regolazione rapidi



PRF_BM

Elementi di ancoraggio, Fissaggio centrale per piede



PM3

Vite senza fine, Acciaio non temprato



WW10

Guida Drylin® W, Carrello



TCSH

Tenditore per catena automatico, Con pattino



PRF_PSP_PR

Profilato di copertura, Da inserire nelle scanalature




SSB

Ingranaggio conico inox, 1:1



BS3

Panamech, Multi-Beam inox, Inox - con



PRF_P

Elementi di ancoraggio, Base di



LRX

Guida lineare a rulli, Carello - da 9410 N a



WS20

Binario Drylin® W, Binario

Prodotti correlati



ALIDRP240

Alimentazione, 10 A



MDPOT

Potenziometro,