

# Simple support base (bipod)



## ESSBNV


## Plastic

- **Bipod support base**
- Component for conveyor structure
- For round tube
- Materials
  - Body: reinforced polyamide
  - Screws: stainless steel 304



### Accessories

- Add compatible **PR** feet to order (tome 5 p.169)



### DISCOUNTS

Qty	1+	5+	10+
Disc. List		-5%	On request

Part number	ØDF	Max. load resistance FM (N)	Max. working load FT (N)	Weight (kg)	Price each 1 to 4
ESSB-42/NV	42,4	15800	9600	0,612	43,57 €
ESSB-48/NV	48,3	15800	9600	0,612	43,57 €
ESSB-50/NV	50,8	15800	9600	0,612	43,57 €
ESSB-60/NV	60,3	15800	9600	0,752	43,57 €

Dimensions in mm

- Combined bipod support part
- Component for conveyor structure
- For round tube
- Materials

Body: reinforced polyamide


Screws: stainless steel 304

### Accessories

- Add compatible PR feet to order (tome 5 p.169)



Typical application



### DISCOUNTS

Qty	1+	5+	10+
Disc.	List	-5%	On request

Part number	ØDF	ØDH	Max load resistance.FM (N)	Max. working load FT (N)	Weight (kg)	Price each 1 to 4
ESCB-42-42/NV	42,4	42,4	15800	9600	0,925	51,82 €
ESCB-48-42/NV	48,3	42,4	15800	9600	0,925	51,82 €
ESCB-48-48/NV	48,3	48,3	15800	9600	0,925	51,82 €
ESCB-50-42/NV	50,8	42,4	15800	9600	0,925	51,82 €
ESCB-50-48/NV	50,8	48,3	15800	9600	0,925	51,82 €
ESCB-60-42/NV	60,3	42,4	15800	9600	0,925	51,82 €
ESCB-60-48/NV	60,3	48,3	15800	9600	0,925	51,82 €

Dimensions in mm


- **High stability**
- Component for conveyor structure
- For round tube
- Materials:

Body: reinforced polyamide



Screws: stainless steel 304

### Accessories

- Add compatible **PR** feet to order (tome 5 p.169)



Typical application



### DISCOUNTS

Qty	1+	5+	10+
Disc.	List	-5%	On request

Part number	ØDF	Max. load resistance FM (N)	Max. working load. FT (N)	Weight (kg)	Price each 1 to 4
ESST-42/NV	42,4	15800	9600	0,975	49,46 €
ESST-48/NV	48,3	15800	9600	0,975	49,46 €
ESST-50/NV	50,8	15800	9600	0,975	49,46 €
ESST-60/NV	60,3	15800	9600	0,975	49,46 €

Dimensions in mm

## Altri prodotti...




PGM52-M4

Maniglia a ponte,  
Alluminio



CHB

Riduttore a ruota e  
vite senza fine, fino a  
22 Nm



M0

Coppia ruota e vite  
senza fine, Plastica  
lavorata (delrin)



SHW

Rondella semplice,  
Acciaio



GGP

Vite ad alette,  
Tecnopolimer con  
inserto in acciaio




BPVM

Sfera portante  
avvitabile miniatura,  
Miniatura ad avvitare



PRF\_ART

Cerniere e giunti,  
Standard



M0

Ruota per vite senza  
fine, Bronzo



SSG2\_304L

Ingranaggio dritto  
Inox, Inox 304L



PARF110

Piede senza snodo,  
Piede snodato



PV1R

Braccio portaventosa  
orientabile, Serraggio



BEAB

Manopola, stella, anti-  
bacterial

## Prodotti correlati



ES

Support base (tripod),  
Plastic



ES

Simple support base  
(bipod), Plastic



PR40

Piede fissabile con  
snodo - poliammide, Ø  
40



PR40

Piede fissabile con  
snodo - poliammide, Ø  
50