

- **Digital speed controller for DC or brushless motors up to 250W**
- Configured using a USB cable and graphical interface

Accessories

- **ESCON Studio** software
(Free download from our site)



ESCON-4Q-50/5



ESCON-USB



ESCON-CABLE

DISCOUNTS

Qty	1+	6+	10+
Disc.	List -7%		On request

Technical Specifications		50V/5A	
- Max power	250W	- Fault	Yes
- Supply voltage	10 to 50 Vdc	- Auxiliary Voltage	+5 Vdc 10 mA max
- Max output current	15A	- Hall sensor supply	+5 Vdc 10 mA max
- Nominal Output current	5A	- Encoder supply	+5 vdc 70mA
- Max motor speed	150 000 rpm	- Aux input supply	-10 /+10 Vdc
- Programmable	No	Parameters	
- Control mode	Current, Speed	- Offset	Yes
Inputs:		- Max speed	Yes
- Limit switches	No	- Max output current	5 A
- Analogue	2,12 bit, +/-10V	- Speed ramp	Yes
- Speed limit	Pot. ext/int, PWM 53.6KHZ	- Current point	15 A
- Enable/Disable	Yes	- Gain	Yes
- Electronic brake	Yes	Protection	
- Stop	No	- Reverse polarity	No
- Direction	Yes	- Surge protection	Yes
- Encoder	A,A/B, B/ -1MHz	- Under voltage	Yes
- Tachometer	Yes	- Overvoltage	Yes
- Regulation	Rxl	- Over Current limit	Limited by regulator
- Serial link	No	- Motor short circuit	Yes
- CAN bus	No	- Input short circuit	Yes
Outputs :		- Supply short circuit	Yes
- USB signal	Mini USB	- Thermal	Yes
- Speed	Yes	- Working temp	-30°/ +45°C
- Current	Yes	- Storage	-40°/ +85°C
- Ready	Yes	- Relative humidity	20/80 % non condensing

Part number	Mounting	Format	Weight (g)	Price each 1 to 5
ESCON-4Q-50/5	Screw M4	115X75,5x24	204	379,04 €
ESCON-USB		USB cable for PC link		22,66 €
ESCON-CABLE		Kit of 4 cables for DC motor		49,44 €

Dimensions in mm

Altri prodotti...



CLLCLLP
Perno serie lunga,
Acciaio - serie lunga




PRT
Corona girevole
Iglidur®, Iglidur®,
alluminio e inox



PTA80
Piede snodato con
base stampata Ø80, Ø
80



Q6
Cuscinetto radiale a
sfere, Acciaio



LSM
Vite trapezoidale inox
316L, Inox - 1 filetto



BL8
Rinvio angolare, da
0.20 a 2 Nm



CHB
Single output shaft,
For CHB gearbox



CHAGC-AL
Cerniera ad avvitare,
Sfilabile



R206
Molla per stampi
ISO10243, Extra-forte



CLAT
Maniglia a ripresa
Hygienic Usit®, Inox



GAL_20
Rullo per
trasportatore,
Polietilene



KB_UU
Manicotto a sfere di
precisione, Di
precisione - acciaio

Prodotti correlati



ESCON
Variatore di velocità
5A, 5 A